

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1261199

Luminaire Tested: P3AS24R609050D010 E3CB1MMS

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1261199  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-40)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS24R609050D010 E3CB1MMS  
Description: 3in Adjustable LED luminaire with, R60 optic, 5000K CCT AND, 90CRI , E3CB1MMS TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2669.0 lumens  
Efficiency: N/A  
Efficacy: 92.7 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.91  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 28.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1261199  
CATALOG NUMBER: P3AS24R609050D010 E3CB1MMS

### Luminous Intensity Polar Plot





TEST NUMBER: P1261199

CATALOG NUMBER: P3AS24R609050D010 E3CB1MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     |     |     | 0   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | 100 | 100 | 100 |
| 1   | 114 | 111 | 108 | 106 | 111 | 109 | 106 | 104 | 105 | 103 | 101 | 101 | 100 | 98  | 97  | 96  | 95  | 94  | 94  | 94  | 94  |
| 2   | 108 | 103 | 99  | 96  | 106 | 102 | 98  | 95  | 98  | 95  | 93  | 95  | 93  | 91  | 93  | 91  | 89  | 87  | 87  | 87  | 87  |
| 3   | 103 | 96  | 91  | 88  | 101 | 95  | 90  | 87  | 92  | 89  | 85  | 90  | 87  | 84  | 88  | 85  | 83  | 81  | 81  | 81  | 81  |
| 4   | 98  | 90  | 85  | 81  | 96  | 89  | 84  | 80  | 87  | 83  | 79  | 85  | 81  | 78  | 83  | 80  | 77  | 76  | 76  | 76  | 76  |
| 5   | 93  | 84  | 79  | 74  | 91  | 84  | 78  | 74  | 82  | 77  | 73  | 80  | 76  | 73  | 79  | 75  | 72  | 71  | 71  | 71  | 71  |
| 6   | 88  | 79  | 73  | 69  | 87  | 79  | 73  | 69  | 77  | 72  | 68  | 76  | 71  | 68  | 74  | 70  | 68  | 66  | 66  | 66  | 66  |
| 7   | 84  | 75  | 69  | 64  | 82  | 74  | 68  | 64  | 73  | 68  | 64  | 71  | 67  | 64  | 70  | 66  | 63  | 62  | 62  | 62  | 62  |
| 8   | 80  | 70  | 64  | 60  | 78  | 70  | 64  | 60  | 69  | 64  | 60  | 68  | 63  | 60  | 67  | 62  | 59  | 58  | 58  | 58  | 58  |
| 9   | 76  | 66  | 61  | 57  | 75  | 66  | 60  | 56  | 65  | 60  | 56  | 64  | 59  | 56  | 63  | 59  | 56  | 55  | 55  | 55  | 55  |
| 10  | 72  | 63  | 57  | 53  | 71  | 62  | 57  | 53  | 62  | 56  | 53  | 61  | 56  | 53  | 60  | 56  | 53  | 51  | 51  | 51  | 51  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 637339 |
| 5°  | 612061 |
| 10° | 630160 |
| 15° | 638278 |
| 20° | 563596 |
| 25° | 474971 |
| 30° | 385224 |
| 35° | 250881 |
| 40° | 115216 |
| 45° | 44160  |
| 50° | 14771  |
| 55° | 3938   |
| 60° | 3640   |
| 65° | 3217   |
| 70° | 2629   |
| 75° | 3474   |
| 80° | 2652   |
| 85° | 5284   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 44160 cd/sqm



TEST NUMBER: P1261199  
 CATALOG NUMBER: P3AS24R609050D010 E3CB1MMS

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 267.6  | 10.0      |
| 10°-20°   | 769.9  | 28.8      |
| 20°-30°   | 898.0  | 33.6      |
| 30°-40°   | 579.5  | 21.7      |
| 40°-50°   | 129.8  | 4.9       |
| 50°-60°   | 13.0   | 0.5       |
| 60°-70°   | 6.1    | 0.2       |
| 70°-80°   | 3.5    | 0.1       |
| 80°-90°   | 1.4    | 0.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1935.6 | 72.5      |
| 0°-40°    | 2515.1 | 94.2      |
| 0°-60°    | 2657.9 | 99.6      |
| 0°-90°    | 2669.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 2669.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 2906 |      |
| 5°  | 2781 | 268  |
| 15° | 2812 | 770  |
| 25° | 1963 | 898  |
| 35° | 937  | 579  |
| 45° | 142  | 130  |
| 55° | 10   | 13   |
| 65° | 6    | 6    |
| 75° | 4    | 4    |
| 85° | 2    | 1    |
| 90° | 0    |      |



TEST NUMBER: P1261199  
CATALOG NUMBER: P3AS24R609050D010 E3CB1MMS

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 2906.5 |
| 2.5°  | 2859.0 |
| 5°    | 2780.6 |
| 7.5°  | 2776.5 |
| 10°   | 2830.1 |
| 12.5° | 2865.2 |
| 15°   | 2811.6 |
| 17.5° | 2650.5 |
| 20°   | 2415.2 |
| 22.5° | 2169.6 |
| 25°   | 1963.1 |
| 27.5° | 1760.8 |
| 30°   | 1521.4 |
| 32.5° | 1240.6 |
| 35°   | 937.2  |
| 37.5° | 639.9  |
| 40°   | 402.5  |
| 42.5° | 241.5  |
| 45°   | 142.4  |
| 47.5° | 82.6   |
| 50°   | 43.3   |
| 52.5° | 14.4   |
| 55°   | 10.3   |
| 57.5° | 8.3    |
| 60°   | 8.3    |
| 62.5° | 6.2    |
| 65°   | 6.2    |
| 67.5° | 6.2    |
| 70°   | 4.1    |
| 72.5° | 4.1    |
| 75°   | 4.1    |
| 77.5° | 2.1    |
| 80°   | 2.1    |
| 82.5° | 2.1    |
| 85°   | 2.1    |
| 87.5° | 0.0    |
| 90°   | 0.0    |

(END OF REPORT)