

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1260524

Luminaire Tested: P3AS17R609050DE010 E3DL1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1260524
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-39)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R609050DE010 E3DL1WMH
Description: 3in Adjustable LED luminaire with, R60 optic, 5000K CCT AND, 90CRI , E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1479.0 lumens
Efficiency: N/A
Efficacy: 69.8 lumens/watt
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1260524

CATALOG NUMBER: P3AS17R609050DE010 E3DL1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1260524

CATALOG NUMBER: P3AS17R609050DE010 E3DL1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	95	89	85	99	93	88	84	91	86	83		88	85	82		86
4	96	88	82	78	94	87	81	77	85	80	76		83	79	75		81
5	91	82	76	71	89	81	75	71	79	74	70		78	73	70		76
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		72
7	82	72	66	61	80	71	65	61	70	65	61		69	64	60		68
8	77	68	61	57	76	67	61	57	66	60	57		65	60	56		64
9	74	64	57	53	72	63	57	53	62	57	53		61	56	53		60
10	70	60	54	50	69	60	54	50	59	53	50		58	53	50		57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	349248
5°	345938
10°	335843
15°	314644
20°	278484
25°	232973
30°	182585
35°	132454
40°	88108
45°	54920
50°	29747
55°	8602
60°	8026
65°	7316
70°	7181
75°	7117
80°	7072
85°	7045

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 54920 cd/sqm

TEST NUMBER: P1260524

CATALOG NUMBER: P3AS17R609050DE010 E3DL1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	148.0	10.0
10°-20°	384.5	26.0
20°-30°	438.3	29.6
30°-40°	310.8	21.0
40°-50°	141.0	9.5
50°-60°	29.9	2.0
60°-70°	14.5	1.0
70°-80°	8.9	0.6
80°-90°	3.0	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	970.8	65.6
0°-40°	1281.6	86.7
0°-60°	1452.6	98.2
0°-90°	1479.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1479.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1593	
5°	1572	148
15°	1386	385
25°	963	438
35°	495	311
45°	177	141
55°	22	30
65°	14	14
75°	8	9
85°	3	3
90°	0	

TEST NUMBER: P1260524

CATALOG NUMBER: P3AS17R609050DE010 E3DL1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1592.7
2.5°	1587.0
5°	1571.6
7.5°	1544.9
10°	1508.3
12.5°	1456.3
15°	1386.0
17.5°	1297.5
20°	1193.4
22.5°	1081.0
25°	962.9
27.5°	842.0
30°	721.1
32.5°	605.9
35°	494.8
37.5°	396.4
40°	307.8
42.5°	233.3
45°	177.1
47.5°	132.1
50°	87.2
52.5°	40.8
55°	22.5
57.5°	19.7
60°	18.3
62.5°	16.9
65°	14.1
67.5°	12.7
70°	11.2
72.5°	9.8
75°	8.4
77.5°	7.0
80°	5.6
82.5°	4.2
85°	2.8
87.5°	1.4
90°	0.0

(END OF REPORT)