

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1260538

Luminaire Tested: P3AS17R659050DE010 E3CB1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1260538
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-44)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R659050DE010 E3CB1MMS
Description: 3in Adjustable LED luminaire with, R65 optic, 5000K CCT AND, 90CRI , E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1740.0 lumens
Efficiency: N/A
Efficacy: 82.1 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.9
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1260538

CATALOG NUMBER: P3AS17R659050DE010 E3CB1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1260538

CATALOG NUMBER: P3AS17R659050DE010 E3CB1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94		
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	90	89	87		
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81		
4	97	90	84	80	96	89	84	80	87	82	79	85	81	78	83	80	77	75		
5	93	84	78	74	91	83	78	74	82	77	73	80	76	73	78	75	72	70		
6	88	79	73	69	86	78	73	69	77	72	68	75	71	68	74	70	67	66		
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62		
8	80	70	64	60	78	69	64	60	68	63	60	67	63	59	66	62	59	58		
9	76	66	60	56	75	66	60	56	65	60	56	64	59	56	63	59	56	54		
10	72	63	57	53	71	62	57	53	61	56	53	60	56	53	60	55	52	51		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	425207
5°	400197
10°	395116
15°	388152
20°	366482
25°	340133
30°	264395
35°	152933
40°	61630
45°	28375
50°	11053
55°	4320
60°	3684
65°	3632
70°	3590
75°	3558
80°	3536
85°	3522

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 28375 cd/sqm

TEST NUMBER: P1260538

CATALOG NUMBER: P3AS17R659050DE010 E3CB1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	172.8	9.9
10°-20°	477.5	27.4
20°-30°	625.0	35.9
30°-40°	362.0	20.8
40°-50°	77.5	4.5
50°-60°	12.6	0.7
60°-70°	6.9	0.4
70°-80°	4.1	0.2
80°-90°	1.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1275.3	73.3
0°-40°	1637.3	94.1
0°-60°	1727.5	99.3
0°-90°	1740.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1740.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1939	
5°	1818	173
15°	1710	477
25°	1406	625
35°	571	362
45°	92	77
55°	11	13
65°	7	7
75°	4	4
85°	1	2
90°	0	

TEST NUMBER: P1260538

CATALOG NUMBER: P3AS17R659050DE010 E3CB1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	1939.1
2.5°	1884.3
5°	1818.1
7.5°	1791.4
10°	1774.5
12.5°	1750.6
15°	1709.8
17.5°	1646.4
20°	1570.5
22.5°	1498.7
25°	1405.8
27.5°	1249.6
30°	1044.2
32.5°	809.2
35°	571.3
37.5°	361.7
40°	215.3
42.5°	135.1
45°	91.5
47.5°	59.1
50°	32.4
52.5°	15.5
55°	11.3
57.5°	9.9
60°	8.4
62.5°	8.4
65°	7.0
67.5°	5.6
70°	5.6
72.5°	4.2
75°	4.2
77.5°	2.8
80°	2.8
82.5°	1.4
85°	1.4
87.5°	1.4
90°	0.0

(END OF REPORT)