

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1260548

Luminaire Tested: P3AS17R659050DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1260548
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-43)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R659050DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R65 optic, 5000K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 691.0 lumens
Efficiency: N/A
Efficacy: 32.6 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1260548

CATALOG NUMBER: P3AS17R659050DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1260548

CATALOG NUMBER: P3AS17R659050DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	95	89	85	99	93	88	84	90	86	83		88	85	82		86
4	96	88	82	78	94	87	81	77	85	80	76		83	79	75		81
5	91	82	76	71	89	81	75	71	79	74	70		77	73	70		76
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		72
7	82	72	66	61	80	71	65	61	70	64	61		69	64	60		67
8	77	67	61	57	76	67	61	57	66	60	57		65	60	56		64
9	74	64	57	53	72	63	57	53	62	57	53		61	56	53		60
10	70	60	54	50	69	59	54	50	59	53	50		58	53	50		57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	162947
5°	160995
10°	154885
15°	145086
20°	130515
25°	110813
30°	86672
35°	61757
40°	40419
45°	24995
50°	12690
55°	4473
60°	3947
65°	3943
70°	3526
75°	3474
80°	3536
85°	3522

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 24995 cd/sqm

TEST NUMBER: P1260548

CATALOG NUMBER: P3AS17R659050DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	68.7	9.9
10°-20°	177.9	25.7
20°-30°	207.9	30.1
30°-40°	145.3	21.0
40°-50°	64.0	9.3
50°-60°	14.2	2.1
60°-70°	7.3	1.1
70°-80°	4.3	0.6
80°-90°	1.5	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	454.4	65.8
0°-40°	599.7	86.8
0°-60°	677.9	98.1
0°-90°	691.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	691.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	743	
5°	731	69
15°	639	178
25°	458	208
35°	231	145
45°	81	64
55°	12	14
65°	8	7
75°	4	4
85°	1	2
90°	0	

TEST NUMBER: P1260548

CATALOG NUMBER: P3AS17R659050DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	743.1
2.5°	740.4
5°	731.4
7.5°	716.3
10°	695.6
12.5°	670.1
15°	639.1
17.5°	601.3
20°	559.3
22.5°	511.7
25°	458.0
27.5°	401.5
30°	342.3
32.5°	285.1
35°	230.7
37.5°	183.2
40°	141.2
42.5°	106.8
45°	80.6
47.5°	59.2
50°	37.2
52.5°	19.3
55°	11.7
57.5°	10.3
60°	9.0
62.5°	8.3
65°	7.6
67.5°	6.2
70°	5.5
72.5°	4.8
75°	4.1
77.5°	3.4
80°	2.8
82.5°	2.1
85°	1.4
87.5°	0.7
90°	0.0

(END OF REPORT)