

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1261219

Luminaire Tested: P3AS24R609050D010 E3DLD1WH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1261219  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-38)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS24R609050D010 E3DLD1WH  
Description: 3in Adjustable LED luminaire with, R60 optic, 5000K CCT AND, 90CRI , E3DLD1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1701.0 lumens  
Efficiency: N/A  
Efficacy: 59.1 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 28.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1261219  
CATALOG NUMBER: P3AS24R609050D010 E3DLD1WH

### Luminous Intensity Polar Plot





TEST NUMBER: P1261219  
 CATALOG NUMBER: P3AS24R609050D010 E3DLD1WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	84	82		
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74		
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67		
5	87	77	70	65	85	76	69	65	74	68	64	72	67	63	71	66	63	61		
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56		
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51		
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47		
9	68	57	51	46	67	57	50	46	56	50	46	55	49	46	54	49	45	44		
10	65	54	47	43	64	53	47	43	52	47	43	52	46	42	51	46	42	41		

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	301949
5°	298568
10°	288216
15°	272306
20°	250995
25°	227263
30°	201778
35°	172421
40°	137114
45°	96661
50°	57755
55°	29208
60°	28068
65°	25684
70°	23850
75°	22706
80°	20836
85°	15599

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 96661 cd/sqm



TEST NUMBER: P1261219  
 CATALOG NUMBER: P3AS24R609050D010 E3DLD1WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	127.5	7.5
10°-20°	335.2	19.7
20°-30°	430.4	25.3
30°-40°	399.1	23.5
40°-50°	242.9	14.3
50°-60°	81.0	4.8
60°-70°	49.3	2.9
70°-80°	27.8	1.6
80°-90°	7.8	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	893.1	52.5
0°-40°	1292.2	76.0
0°-60°	1616.1	95.0
0°-90°	1701.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1701.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1377	
5°	1356	127
15°	1200	335
25°	939	430
35°	644	399
45°	312	243
55°	76	81
65°	50	49
75°	27	28
85°	6	8
90°	0	



TEST NUMBER: P1261219  
CATALOG NUMBER: P3AS24R609050D010 E3DLD1WH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1377.0
2.5°	1370.8
5°	1356.4
7.5°	1329.5
10°	1294.4
12.5°	1251.1
15°	1199.5
17.5°	1139.6
20°	1075.6
22.5°	1007.5
25°	939.3
27.5°	869.1
30°	796.9
32.5°	724.6
35°	644.1
37.5°	559.5
40°	479.0
42.5°	394.3
45°	311.7
47.5°	241.5
50°	169.3
52.5°	101.2
55°	76.4
57.5°	70.2
60°	64.0
62.5°	55.7
65°	49.5
67.5°	43.4
70°	37.2
72.5°	31.0
75°	26.8
77.5°	20.6
80°	16.5
82.5°	10.3
85°	6.2
87.5°	4.1
90°	0.0

(END OF REPORT)