

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1260639

Luminaire Tested: P3AS20R209050D010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1260639
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-6)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R209050D010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R20 optic, 5000K CCT AND, 90CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 712.0 lumens
Efficiency: N/A
Efficacy: 24.7 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1260639

CATALOG NUMBER: P3AS20R209050D010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1260639

CATALOG NUMBER: P3AS20R209050D010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	94	91	95	92	89		92	89	87		90
3	100	93	87	82	98	91	86	82	88	84	80		86	82	79		84
4	94	86	79	75	92	85	79	74	82	77	73		80	76	72		78
5	89	80	73	68	87	79	73	68	77	71	67		75	70	67		73
6	84	74	68	63	82	73	67	63	72	66	62		70	65	62		69
7	80	69	63	58	78	69	62	58	67	62	58		66	61	57		65
8	75	65	59	54	74	64	58	54	63	58	54		62	57	53		61
9	72	61	55	50	70	61	55	50	60	54	50		59	54	50		58
10	68	58	51	47	67	57	51	47	56	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	176104
5°	171406
10°	157690
15°	138798
20°	119034
25°	99998
30°	80848
35°	61489
40°	43768
45°	28902
50°	17910
55°	11775
60°	10701
65°	9858
70°	9296
75°	8388
80°	7956
85°	6793

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 28902 cd/sqm

TEST NUMBER: P1260639

CATALOG NUMBER: P3AS20R209050D010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.0	10.1
10°-20°	170.2	23.9
20°-30°	188.9	26.5
30°-40°	144.1	20.2
40°-50°	73.8	10.4
50°-60°	30.3	4.3
60°-70°	18.9	2.7
70°-80°	10.6	1.5
80°-90°	3.1	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	431.2	60.6
0°-40°	575.3	80.8
0°-60°	679.4	95.4
0°-90°	712.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	712.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	803	
5°	779	72
15°	611	170
25°	413	189
35°	230	144
45°	93	74
55°	31	30
65°	19	19
75°	10	11
85°	3	3
90°	0	

TEST NUMBER: P1260639

CATALOG NUMBER: P3AS20R209050D010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	803.1
1°	804.0
2°	800.4
3°	795.9
4°	788.7
5°	778.7
6°	767.0
7°	754.3
8°	740.7
9°	724.5
10°	708.2
12.5°	661.1
15°	611.4
17.5°	560.8
20°	510.1
22.5°	459.5
25°	413.3
27.5°	367.2
30°	319.3
32.5°	274.0
35°	229.7
37.5°	190.8
40°	152.9
42.5°	120.3
45°	93.2
47.5°	70.5
50°	52.5
52.5°	38.9
55°	30.8
57.5°	28.0
60°	24.4
62.5°	21.7
65°	19.0
67.5°	16.3
70°	14.5
72.5°	11.8
75°	9.9
77.5°	8.1
80°	6.3
82.5°	4.5
85°	2.7
87.5°	0.9
90°	0.0

(END OF REPORT)