

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246430

Luminaire Tested: P3AS09R209024DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1246430
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-6)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R209024DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R20 optic, 2400K CCT AND, 90CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 507.9 lumens
Efficiency: N/A
Efficacy: 45.8 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1246430

CATALOG NUMBER: P3AS09R209024DE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1246430

CATALOG NUMBER: P3AS09R209024DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	94	91	95	92	89		92	89	87		90
3	100	93	87	82	98	91	86	82	88	84	80		86	82	79		84
4	94	86	79	75	92	85	79	74	82	77	73		80	76	72		78
5	89	80	73	68	87	79	73	68	77	71	67		75	70	67		73
6	84	74	68	63	82	73	67	63	72	66	62		70	65	62		69
7	80	69	63	58	78	69	62	58	67	62	58		66	61	57		65
8	75	65	59	54	74	64	58	54	63	58	54		62	57	53		61
9	72	61	55	50	70	61	55	50	60	54	50		59	54	50		58
10	68	58	51	47	67	57	51	47	56	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	125648
5°	122298
10°	112512
15°	99024
20°	84941
25°	71351
30°	57680
35°	43875
40°	31230
45°	20622
50°	12759
55°	8372
60°	7631
65°	7057
70°	6604
75°	6015
80°	5683
85°	4780

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 20622 cd/sqm

TEST NUMBER: P1246430

CATALOG NUMBER: P3AS09R209024DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.4	10.1
10°-20°	121.4	23.9
20°-30°	134.8	26.5
30°-40°	102.8	20.2
40°-50°	52.7	10.4
50°-60°	21.6	4.3
60°-70°	13.5	2.7
70°-80°	7.6	1.5
80°-90°	2.2	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	307.6	60.6
0°-40°	410.5	80.8
0°-60°	484.7	95.4
0°-90°	507.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	507.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	573	
5°	556	51
15°	436	121
25°	295	135
35°	164	103
45°	66	53
55°	22	22
65°	14	13
75°	7	8
85°	2	2
90°	0	

TEST NUMBER: P1246430

CATALOG NUMBER: P3AS09R209024DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	573.0
1°	573.7
2°	571.1
3°	567.9
4°	562.7
5°	555.6
6°	547.2
7°	538.2
8°	528.5
9°	516.9
10°	505.3
12.5°	471.7
15°	436.2
17.5°	400.1
20°	364.0
22.5°	327.8
25°	294.9
27.5°	262.0
30°	227.8
32.5°	195.5
35°	163.9
37.5°	136.2
40°	109.1
42.5°	85.8
45°	66.5
47.5°	50.3
50°	37.4
52.5°	27.7
55°	21.9
57.5°	20.0
60°	17.4
62.5°	15.5
65°	13.6
67.5°	11.6
70°	10.3
72.5°	8.4
75°	7.1
77.5°	5.8
80°	4.5
82.5°	3.2
85°	1.9
87.5°	0.6
90°	0.0

(END OF REPORT)