

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246467

Luminaire Tested: P3AS09R309024DE010 E3CB1MB

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1246467
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-16)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R309024DE010 E3CB1MB
Description: 3in Adjustable LED luminaire with, R30 optic, 2400K CCT AND, 90CRI , E3CB1MB TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 821.9 lumens
Efficiency: N/A
Efficacy: 74.0 lumens/watt
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.47
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1246467
CATALOG NUMBER: P3AS09R309024DE010 E3CB1MB

Luminous Intensity Polar Plot





TEST NUMBER: P1246467

CATALOG NUMBER: P3AS09R309024DE010 E3CB1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98	100
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	98	96	95	97
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	95	94	92	94
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	94	92	93	91	89	91
4	105	100	96	93	103	99	95	92	97	94	91	95	92	90	93	91	89	93	91	89	88
5	102	96	92	89	100	95	92	89	94	90	88	92	89	87	91	88	87	91	88	87	85
6	99	93	89	86	98	92	88	86	91	88	85	90	87	85	89	86	84	89	86	84	83
7	96	90	86	83	95	89	86	83	88	85	83	87	84	82	86	84	82	86	84	82	81
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	84	82	80	79
9	91	85	81	78	90	84	81	78	84	80	78	83	80	78	82	79	77	82	79	77	77
10	89	83	79	76	88	82	78	76	82	78	76	81	78	76	80	77	75	80	77	75	75

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	669376
5°	656745
10°	581374
15°	368334
20°	139825
25°	41398
30°	16357
35°	5006
40°	2204
45°	806
50°	648
55°	497
60°	570
65°	675
70°	385
75°	508
80°	758
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 806 cd/sqm



TEST NUMBER: P1246467
 CATALOG NUMBER: P3AS09R309024DE010 E3CB1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	274.3	33.4
10°-20°	427.4	52.0
20°-30°	99.3	12.1
30°-40°	15.4	1.9
40°-50°	2.6	0.3
50°-60°	1.2	0.1
60°-70°	1.0	0.1
70°-80°	0.6	0.1
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	801.0	97.4
0°-40°	816.3	99.3
0°-60°	820.2	99.8
0°-90°	821.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	821.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3053	
5°	2984	274
15°	1622	427
25°	171	99
35°	19	15
45°	3	3
55°	1	1
65°	1	1
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1246467
CATALOG NUMBER: P3AS09R309024DE010 E3CB1MB

CANDELA DISTRIBUTION (FULL):

0°	
0°	3052.6
1°	3050.7
2°	3042.3
3°	3028.1
4°	3010.0
5°	2983.6
6°	2950.6
7°	2901.6
8°	2834.4
9°	2735.6
10°	2611.0
11°	2450.2
12°	2268.8
13°	2067.4
14°	1845.9
15°	1622.5
17.5°	1061.5
20°	599.2
22.5°	306.0
25°	171.1
27.5°	105.2
30°	64.6
32.5°	34.9
35°	18.7
37.5°	12.3
40°	7.7
42.5°	4.5
45°	2.6
47.5°	1.9
50°	1.9
52.5°	1.3
55°	1.3
57.5°	1.3
60°	1.3
62.5°	1.3
65°	1.3
67.5°	0.6
70°	0.6
72.5°	0.6
75°	0.6
77.5°	0.6
80°	0.6
82.5°	0.0
85°	0.0
87.5°	0.0



TEST NUMBER: P1246467
CATALOG NUMBER: P3AS09R309024DE010 E3CB1MB

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)