

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1247408

Luminaire Tested: P3AS17R559024DE010 E3D1WH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1247408
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-14)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R559024DE010 E3D1WH
Description: 3in Adjustable LED luminaire with, R55 optic, 2400K CCT AND, 90CRI , E3D1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1466.1 lumens
Efficiency: N/A
Efficacy: 69.2 lumens/watt
Spacing Criteria (0/90/45): 0.93 / 0.93 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1247408
CATALOG NUMBER: P3AS17R559024DE010 E3D1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1247408
 CATALOG NUMBER: P3AS17R559024DE010 E3D1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 102 | 102 | 102 | 100 |
| 1 | 114 | 111 | 109 | 107 | 112 | 109 | 107 | 105 | 105 | 104 | 102 | 102 | 100 | 99 | 98 | 97 | 96 | 96 | 96 | 96 | 95 |
| 2 | 109 | 105 | 101 | 98 | 107 | 103 | 100 | 97 | 100 | 97 | 95 | 97 | 95 | 93 | 94 | 92 | 91 | 91 | 91 | 91 | 89 |
| 3 | 104 | 98 | 94 | 90 | 102 | 97 | 93 | 90 | 95 | 91 | 88 | 92 | 89 | 87 | 90 | 88 | 86 | 86 | 86 | 86 | 84 |
| 4 | 100 | 93 | 88 | 84 | 98 | 92 | 87 | 84 | 90 | 86 | 83 | 88 | 84 | 82 | 86 | 83 | 81 | 81 | 81 | 81 | 79 |
| 5 | 95 | 88 | 82 | 79 | 94 | 87 | 82 | 78 | 85 | 81 | 78 | 84 | 80 | 77 | 82 | 79 | 76 | 76 | 76 | 76 | 75 |
| 6 | 91 | 83 | 78 | 74 | 90 | 82 | 77 | 74 | 81 | 76 | 73 | 80 | 76 | 73 | 78 | 75 | 72 | 72 | 72 | 72 | 71 |
| 7 | 87 | 79 | 73 | 70 | 86 | 78 | 73 | 69 | 77 | 72 | 69 | 76 | 72 | 69 | 75 | 71 | 68 | 68 | 68 | 68 | 67 |
| 8 | 83 | 75 | 69 | 66 | 82 | 74 | 69 | 65 | 73 | 69 | 65 | 72 | 68 | 65 | 71 | 68 | 65 | 65 | 65 | 65 | 63 |
| 9 | 80 | 71 | 66 | 62 | 79 | 71 | 66 | 62 | 70 | 65 | 62 | 69 | 65 | 62 | 68 | 64 | 61 | 61 | 61 | 61 | 60 |
| 10 | 77 | 68 | 62 | 59 | 76 | 67 | 62 | 59 | 67 | 62 | 59 | 66 | 62 | 59 | 65 | 61 | 58 | 58 | 58 | 58 | 57 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 425119 |
| 5° | 410080 |
| 10° | 424731 |
| 15° | 418754 |
| 20° | 387554 |
| 25° | 313421 |
| 30° | 187826 |
| 35° | 63657 |
| 40° | 17547 |
| 45° | 7784 |
| 50° | 2286 |
| 55° | 421 |
| 60° | 263 |
| 65° | 311 |
| 70° | 385 |
| 75° | 0 |
| 80° | 0 |
| 85° | 0 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 7784 cd/sqm



TEST NUMBER: P1247408
 CATALOG NUMBER: P3AS17R559024DE010 E3D1WH

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 180.2 | 12.3 |
| 10°-20° | 513.6 | 35.0 |
| 20°-30° | 570.9 | 38.9 |
| 30°-40° | 177.7 | 12.1 |
| 40°-50° | 21.3 | 1.5 |
| 50°-60° | 1.7 | 0.1 |
| 60°-70° | 0.6 | 0.0 |
| 70°-80° | 0.1 | 0.0 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 1264.7 | 86.3 |
| 0°-40° | 1442.4 | 98.4 |
| 0°-60° | 1465.4 | 100.0 |
| 0°-90° | 1466.1 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 1466.1 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 1939 | |
| 5° | 1863 | 180 |
| 15° | 1845 | 514 |
| 25° | 1295 | 571 |
| 35° | 238 | 178 |
| 45° | 25 | 21 |
| 55° | 1 | 2 |
| 65° | 1 | 1 |
| 75° | 0 | 0 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P1247408
CATALOG NUMBER: P3AS17R559024DE010 E3D1WH

CANDELA DISTRIBUTION (FULL):

| 0° | |
|-------|--------|
| 0° | 1938.7 |
| 1° | 1931.5 |
| 2° | 1912.5 |
| 3° | 1889.1 |
| 4° | 1868.0 |
| 5° | 1863.0 |
| 6° | 1868.5 |
| 7° | 1880.2 |
| 8° | 1893.6 |
| 9° | 1904.2 |
| 10° | 1907.5 |
| 11° | 1905.3 |
| 12° | 1896.4 |
| 13° | 1882.5 |
| 14° | 1866.3 |
| 15° | 1844.6 |
| 16° | 1819.5 |
| 17° | 1787.8 |
| 18° | 1752.1 |
| 19° | 1709.3 |
| 20° | 1660.8 |
| 21° | 1605.7 |
| 22° | 1540.5 |
| 23° | 1468.7 |
| 24° | 1386.2 |
| 25° | 1295.4 |
| 26° | 1195.8 |
| 27° | 1089.9 |
| 28° | 976.9 |
| 29° | 860.5 |
| 30° | 741.8 |
| 31° | 622.7 |
| 32° | 506.3 |
| 32.5° | 454.5 |
| 33° | 401.0 |
| 34° | 310.2 |
| 35° | 237.8 |
| 36° | 181.0 |
| 37° | 134.2 |
| 37.5° | 114.7 |
| 38° | 99.7 |
| 39° | 75.7 |
| 40° | 61.3 |
| 42.5° | 39.0 |
| 45° | 25.1 |



TEST NUMBER: P1247408
CATALOG NUMBER: P3AS17R559024DE010 E3D1WH

CANDELA DISTRIBUTION (continued):

| | 0° |
|-------|------|
| 47.5° | 15.0 |
| 50° | 6.7 |
| 52.5° | 2.2 |
| 55° | 1.1 |
| 57.5° | 0.6 |
| 60° | 0.6 |
| 62.5° | 0.6 |
| 65° | 0.6 |
| 67.5° | 0.6 |
| 70° | 0.6 |
| 72.5° | 0.0 |
| 75° | 0.0 |
| 77.5° | 0.0 |
| 80° | 0.0 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |

(END OF REPORT)