

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1247409

Luminaire Tested: P3AS17R559024DE010 E3D1WMH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1247409
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-14)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R559024DE010 E3D1WMH
Description: 3in Adjustable LED luminaire with, R55 optic, 2400K CCT AND, 90CRI , E3D1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1466.1 lumens
Efficiency: N/A
Efficacy: 69.2 lumens/watt
Spacing Criteria (0/90/45): 0.93 / 0.93 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1247409

CATALOG NUMBER: P3AS17R559024DE010 E3D1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1247409

CATALOG NUMBER: P3AS17R559024DE010 E3D1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	112	109	107	105	105	104	102		102	100	99		98
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		94
3	104	98	94	90	102	97	93	90	95	91	88		92	89	87		90
4	100	93	88	84	98	92	87	84	90	86	83		88	84	82		86
5	95	88	82	79	94	87	82	78	85	81	78		84	80	77		82
6	91	83	78	74	90	82	77	74	81	76	73		80	76	73		78
7	87	79	73	70	86	78	73	69	77	72	69		76	72	69		75
8	83	75	69	66	82	74	69	65	73	69	65		72	68	65		71
9	80	71	66	62	79	71	66	62	70	65	62		69	65	62		68
10	77	68	62	59	76	67	62	59	67	62	59		66	62	59		65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	425119
5°	410080
10°	424731
15°	418754
20°	387554
25°	313421
30°	187826
35°	63657
40°	17547
45°	7784
50°	2286
55°	421
60°	263
65°	311
70°	385
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7784 cd/sqm

TEST NUMBER: P1247409

CATALOG NUMBER: P3AS17R559024DE010 E3D1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	180.2	12.3
10°-20°	513.6	35.0
20°-30°	570.9	38.9
30°-40°	177.7	12.1
40°-50°	21.3	1.5
50°-60°	1.7	0.1
60°-70°	0.6	0.0
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1264.7	86.3
0°-40°	1442.4	98.4
0°-60°	1465.4	100.0
0°-90°	1466.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1466.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1939	
5°	1863	180
15°	1845	514
25°	1295	571
35°	238	178
45°	25	21
55°	1	2
65°	1	1
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1247409

CATALOG NUMBER: P3AS17R559024DE010 E3D1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1938.7
1°	1931.5
2°	1912.5
3°	1889.1
4°	1868.0
5°	1863.0
6°	1868.5
7°	1880.2
8°	1893.6
9°	1904.2
10°	1907.5
11°	1905.3
12°	1896.4
13°	1882.5
14°	1866.3
15°	1844.6
16°	1819.5
17°	1787.8
18°	1752.1
19°	1709.3
20°	1660.8
21°	1605.7
22°	1540.5
23°	1468.7
24°	1386.2
25°	1295.4
26°	1195.8
27°	1089.9
28°	976.9
29°	860.5
30°	741.8
31°	622.7
32°	506.3
32.5°	454.5
33°	401.0
34°	310.2
35°	237.8
36°	181.0
37°	134.2
37.5°	114.7
38°	99.7
39°	75.7
40°	61.3
42.5°	39.0
45°	25.1



TEST NUMBER: P1247409

CATALOG NUMBER: P3AS17R559024DE010 E3D1WMH

CANDELA DISTRIBUTION (continued):

	0°
47.5°	15.0
50°	6.7
52.5°	2.2
55°	1.1
57.5°	0.6
60°	0.6
62.5°	0.6
65°	0.6
67.5°	0.6
70°	0.6
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)