

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1247479

Luminaire Tested: P3AS17R659024DE010 E3DLD1WMH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1247479  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-42)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R659024DE010 E3DLD1WMH  
Description: 3in Adjustable LED luminaire with, R65 optic, 2400K CCT AND, 90CRI , E3DLD1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 894.0 lumens  
Efficiency: N/A  
Efficacy: 42.2 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 21.2  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1247479  
CATALOG NUMBER: P3AS17R659024DE010 E3DLD1WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P1247479

CATALOG NUMBER: P3AS17R659024DE010 E3DLD1WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	93	91	91	91	91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	84	82	82	82	82
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74	74	74	74
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67	67	67	67
5	87	77	70	65	85	76	69	65	74	68	64	72	67	63	71	66	63	61	61	61	61
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56	56	56	56
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51	51	51	51
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47	47	47	47
9	68	57	51	46	67	57	50	46	56	50	46	55	49	46	54	49	45	44	44	44	44
10	65	54	47	43	64	53	47	43	52	47	43	52	46	42	51	46	42	41	41	41	41

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	159088
5°	156944
10°	151678
15°	143043
20°	131938
25°	119765
30°	106092
35°	90266
40°	71820
45°	50703
50°	29440
55°	16057
60°	14955
65°	13542
70°	12374
75°	11522
80°	9976
85°	8554

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 50703 cd/sqm



TEST NUMBER: P1247479

CATALOG NUMBER: P3AS17R659024DE010 E3DLD1WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	67.1	7.5
10°-20°	176.3	19.7
20°-30°	226.6	25.3
30°-40°	209.6	23.4
40°-50°	126.5	14.2
50°-60°	43.2	4.8
60°-70°	26.0	2.9
70°-80°	14.7	1.6
80°-90°	4.2	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	469.9	52.6
0°-40°	679.5	76.0
0°-60°	849.2	95.0
0°-90°	894.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	894.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	726	
5°	713	67
15°	630	176
25°	495	227
35°	337	210
45°	164	127
55°	42	43
65°	26	26
75°	14	15
85°	3	4
90°	0	



TEST NUMBER: P1247479  
CATALOG NUMBER: P3AS17R659024DE010 E3DLD1WMH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	725.5
2.5°	722.1
5°	713.0
7.5°	699.4
10°	681.2
12.5°	658.5
15°	630.1
17.5°	599.5
20°	565.4
22.5°	530.2
25°	495.0
27.5°	457.6
30°	419.0
32.5°	380.4
35°	337.2
37.5°	295.2
40°	250.9
42.5°	206.6
45°	163.5
47.5°	123.8
50°	86.3
52.5°	54.5
55°	42.0
57.5°	37.5
60°	34.1
62.5°	29.5
65°	26.1
67.5°	22.7
70°	19.3
72.5°	17.0
75°	13.6
77.5°	11.4
80°	7.9
82.5°	5.7
85°	3.4
87.5°	2.3
90°	0.0

(END OF REPORT)