

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1260768

Luminaire Tested: P3AS20R409050D010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1260768
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-23)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R409050D010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R40 optic, 5000K CCT AND, 90CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2151.0 lumens
Efficiency: N/A
Efficacy: 74.7 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 0.65 / 0.63
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1260768

CATALOG NUMBER: P3AS20R409050D010 E3DLP1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1260768

CATALOG NUMBER: P3AS20R409050D010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	112	109	107	105	105	104	102		102	100	99		98
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		94
3	104	99	94	91	102	97	93	90	95	91	88		92	89	87		90
4	100	93	88	85	98	92	88	84	90	86	83		88	85	82		86
5	96	88	83	79	94	88	83	79	86	82	78		84	81	78		83
6	92	84	79	75	91	83	78	75	82	78	74		81	77	74		79
7	88	80	75	71	87	79	74	71	78	74	71		77	73	70		76
8	85	76	71	68	84	76	71	67	75	70	67		74	70	67		73
9	82	73	68	64	81	73	68	64	72	67	64		71	67	64		70
10	78	70	65	62	78	70	65	61	69	64	61		68	64	61		67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	951810
5°	924145
10°	838640
15°	692830
20°	499773
25°	309115
30°	167368
35°	86491
40°	47031
45°	26328
50°	13236
55°	9863
60°	8903
65°	8613
70°	8271
75°	7795
80°	6945
85°	4529

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 26328 cd/sqm

TEST NUMBER: P1260768

CATALOG NUMBER: P3AS20R409050D010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	387.0	18.0
10°-20°	831.0	38.6
20°-30°	593.0	27.6
30°-40°	218.3	10.1
40°-50°	68.7	3.2
50°-60°	23.9	1.1
60°-70°	16.5	0.8
70°-80°	9.7	0.5
80°-90°	2.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1811.1	84.2
0°-40°	2029.4	94.3
0°-60°	2122.0	98.7
0°-90°	2151.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2151.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4341	
5°	4198	387
15°	3052	831
25°	1278	593
35°	323	218
45°	85	69
55°	26	24
65°	17	16
75°	9	10
85°	2	3
90°	0	

TEST NUMBER: P1260768

CATALOG NUMBER: P3AS20R409050D010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	4340.6
2.5°	4307.3
5°	4198.4
7.5°	4017.5
10°	3766.4
12.5°	3447.0
15°	3051.9
17.5°	2608.8
20°	2141.7
22.5°	1681.9
25°	1277.6
27.5°	937.9
30°	661.0
32.5°	463.4
35°	323.1
37.5°	228.9
40°	164.3
42.5°	118.2
45°	84.9
47.5°	57.2
50°	38.8
52.5°	27.7
55°	25.8
57.5°	24.0
60°	20.3
62.5°	18.5
65°	16.6
67.5°	14.8
70°	12.9
72.5°	11.1
75°	9.2
77.5°	7.4
80°	5.5
82.5°	3.7
85°	1.8
87.5°	1.8
90°	0.0

(END OF REPORT)