

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1247637

Luminaire Tested: P3AS20R359024D010 E3CD1MMS

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1247637  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-20)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS20R359024D010 E3CD1MMS  
Description: 3in Adjustable LED luminaire with, R35 optic, 2400K CCT AND, 90CRI , E3CD1MMS TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1893.1 lumens  
Efficiency: N/A  
Efficacy: 65.7 lumens/watt  
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.52  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 28.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1247637  
CATALOG NUMBER: P3AS20R359024D010 E3CD1MMS

### Luminous Intensity Polar Plot





TEST NUMBER: P1247637

CATALOG NUMBER: P3AS20R359024D010 E3CD1MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96	96	96	96
2	111	107	104	101	109	105	103	100	102	100	98	99	98	96	97	95	94	93	93	93	93
3	107	102	98	95	105	101	97	95	98	96	93	96	94	92	94	92	90	89	89	89	89
4	104	98	94	91	102	97	93	90	95	92	89	93	90	88	91	89	87	86	86	86	86
5	100	94	90	87	99	93	89	86	92	88	86	90	87	85	89	86	84	83	83	83	83
6	97	91	86	83	96	90	86	83	89	85	82	87	84	82	86	83	81	80	80	80	80
7	94	87	83	80	93	87	83	80	86	82	79	85	81	79	84	81	79	77	77	77	77
8	91	84	80	77	90	84	80	77	83	79	77	82	79	76	81	78	76	75	75	75	75
9	89	82	77	74	88	81	77	74	80	77	74	80	76	74	79	76	74	73	73	73	73
10	86	79	75	72	85	79	75	72	78	74	72	77	74	72	77	74	71	70	70	70	70

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1234353
5°	1209220
10°	1124940
15°	824749
20°	422323
25°	152210
30°	59275
35°	20746
40°	8530
45°	2326
50°	2047
55°	2294
60°	1974
65°	1557
70°	1923
75°	2542
80°	1894
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 75°  
 Luminance: 2542 cd/sqm



TEST NUMBER: P1247637  
 CATALOG NUMBER: P3AS20R359024D010 E3CD1MMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	512.1	27.1
10°-20°	960.9	50.8
20°-30°	340.2	18.0
30°-40°	59.6	3.1
40°-50°	8.7	0.5
50°-60°	4.9	0.3
60°-70°	3.5	0.2
70°-80°	2.6	0.1
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1813.2	95.8
0°-40°	1872.8	98.9
0°-60°	1886.4	99.6
0°-90°	1893.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1893.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5629	
5°	5494	512
15°	3633	961
25°	629	340
35°	78	60
45°	8	9
55°	6	5
65°	3	4
75°	3	3
85°	0	1
90°	0	



TEST NUMBER: P1247637  
CATALOG NUMBER: P3AS20R359024D010 E3CD1MMS

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	5629.1
1°	5627.6
2°	5609.8
3°	5575.5
4°	5544.2
5°	5493.5
6°	5441.3
7°	5383.2
8°	5311.6
9°	5199.8
10°	5052.2
11°	4848.0
12°	4602.0
13°	4309.8
14°	3987.8
15°	3633.0
17.5°	2705.7
20°	1809.8
22.5°	1091.2
25°	629.1
27.5°	375.7
30°	234.1
32.5°	135.7
35°	77.5
37.5°	49.2
40°	29.8
42.5°	14.9
45°	7.5
47.5°	6.0
50°	6.0
52.5°	6.0
55°	6.0
57.5°	4.5
60°	4.5
62.5°	4.5
65°	3.0
67.5°	3.0
70°	3.0
72.5°	3.0
75°	3.0
77.5°	1.5
80°	1.5
82.5°	1.5
85°	0.0
87.5°	0.0



TEST NUMBER: P1247637  
CATALOG NUMBER: P3AS20R359024D010 E3CD1MMS

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)