

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1260783

Luminaire Tested: P3AS20R459050D010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1260783
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-26)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R459050D010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R45 optic, 5000K CCT AND, 90CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 785.0 lumens
Efficiency: N/A
Efficacy: 27.3 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.92
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1260783

CATALOG NUMBER: P3AS20R459050D010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1260783

CATALOG NUMBER: P3AS20R459050D010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89
3	99	92	86	82	97	90	85	81	88	83	80		85	81	78		83
4	94	85	78	74	92	84	78	73	81	76	72		79	75	71		77
5	88	79	72	67	86	78	71	67	76	70	66		74	69	65		72
6	83	73	66	61	81	72	66	61	71	65	61		69	64	60		68
7	78	68	61	57	77	67	61	56	66	60	56		65	60	56		64
8	74	64	57	52	73	63	57	52	62	56	52		61	56	52		60
9	70	60	53	49	69	59	53	49	58	52	48		57	52	48		56
10	67	56	50	45	66	56	49	45	55	49	45		54	49	45		53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	166434
5°	163482
10°	154707
15°	141090
20°	124774
25°	108345
30°	93002
35°	77497
40°	57737
45°	35353
50°	16341
55°	12807
60°	12280
65°	11259
70°	10450
75°	9997
80°	9092
85°	6793

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 35353 cd/sqm

TEST NUMBER: P1260783

CATALOG NUMBER: P3AS20R459050D010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	69.4	8.8
10°-20°	173.0	22.0
20°-30°	205.6	26.2
30°-40°	178.6	22.8
40°-50°	89.6	11.4
50°-60°	31.1	4.0
60°-70°	21.8	2.8
70°-80°	12.2	1.6
80°-90°	3.7	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	448.0	57.1
0°-40°	626.6	79.8
0°-60°	747.3	95.2
0°-90°	785.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	785.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	759	
5°	743	69
15°	622	173
25°	448	206
35°	290	179
45°	114	90
55°	34	31
65°	22	22
75°	12	12
85°	3	4
90°	0	

TEST NUMBER: P1260783

CATALOG NUMBER: P3AS20R459050D010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	759.0
2.5°	755.4
5°	742.7
7.5°	722.8
10°	694.8
12.5°	660.4
15°	621.5
17.5°	578.1
20°	534.7
22.5°	490.3
25°	447.8
27.5°	407.1
30°	367.3
32.5°	329.3
35°	289.5
37.5°	247.0
40°	201.7
42.5°	157.4
45°	114.0
47.5°	75.1
50°	47.9
52.5°	37.1
55°	33.5
57.5°	30.8
60°	28.0
62.5°	25.3
65°	21.7
67.5°	19.0
70°	16.3
72.5°	13.6
75°	11.8
77.5°	9.0
80°	7.2
82.5°	5.4
85°	2.7
87.5°	1.8
90°	0.0

(END OF REPORT)