

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1260788

Luminaire Tested: P3AS20R459050D010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1260788
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-26)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R459050D010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R45 optic, 5000K CCT AND, 90CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1602.0 lumens
Efficiency: N/A
Efficacy: 55.6 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.92
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1260788

CATALOG NUMBER: P3AS20R459050D010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1260788

CATALOG NUMBER: P3AS20R459050D010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89
3	99	92	86	82	97	90	85	81	88	83	80		85	81	78		83
4	94	85	78	74	92	84	78	73	81	76	72		79	75	71		77
5	88	79	72	67	86	78	71	67	76	70	66		74	69	65		72
6	83	73	66	61	81	72	66	61	71	65	61		69	64	60		68
7	78	68	61	57	77	67	61	56	66	60	56		65	60	56		64
8	74	64	57	52	73	63	57	52	62	56	52		61	56	52		60
9	70	60	53	49	69	59	53	49	58	52	48		57	52	48		56
10	67	56	50	45	66	56	49	45	55	49	45		54	49	45		53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	339666
5°	333633
10°	315714
15°	287924
20°	254612
25°	221118
30°	189801
35°	158153
40°	117849
45°	72132
50°	33364
55°	26111
60°	25086
65°	22986
70°	21286
75°	20334
80°	18689
85°	13838

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 72132 cd/sqm

TEST NUMBER: P1260788

CATALOG NUMBER: P3AS20R459050D010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	141.6	8.8
10°-20°	353.1	22.0
20°-30°	419.6	26.2
30°-40°	364.5	22.8
40°-50°	182.8	11.4
50°-60°	63.5	4.0
60°-70°	44.5	2.8
70°-80°	24.8	1.6
80°-90°	7.5	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	914.3	57.1
0°-40°	1278.8	79.8
0°-60°	1525.1	95.2
0°-90°	1602.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1602.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1549	
5°	1516	142
15°	1268	353
25°	914	420
35°	591	365
45°	233	183
55°	68	63
65°	44	45
75°	24	25
85°	6	8
90°	0	

TEST NUMBER: P1260788

CATALOG NUMBER: P3AS20R459050D010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1549.0
2.5°	1541.6
5°	1515.7
7.5°	1475.1
10°	1417.9
12.5°	1347.7
15°	1268.3
17.5°	1179.7
20°	1091.1
22.5°	1000.6
25°	913.9
27.5°	830.8
30°	749.6
32.5°	672.0
35°	590.8
37.5°	504.0
40°	411.7
42.5°	321.2
45°	232.6
47.5°	153.2
50°	97.8
52.5°	75.7
55°	68.3
57.5°	62.8
60°	57.2
62.5°	51.7
65°	44.3
67.5°	38.8
70°	33.2
72.5°	27.7
75°	24.0
77.5°	18.5
80°	14.8
82.5°	11.1
85°	5.5
87.5°	3.7
90°	0.0

(END OF REPORT)