

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1260789

Luminaire Tested: P3AS20R459050D010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1260789
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-25)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R459050D010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R45 optic, 5000K CCT AND, 90CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 652.9 lumens
Efficiency: N/A
Efficacy: 22.7 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1260789
CATALOG NUMBER: P3AS20R459050D010 E3DLP1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1260789

CATALOG NUMBER: P3AS20R459050D010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93				93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	86				86
3	102	95	90	85	100	93	89	85	91	87	83	88	85	82	86	83	81	79				79
4	96	88	83	78	94	87	82	78	85	81	77	83	79	76	81	78	75	74				74
5	91	83	77	72	90	82	76	72	80	75	71	78	74	71	77	73	70	69				69
6	87	78	72	67	85	77	71	67	75	70	66	74	69	66	73	69	66	64				64
7	83	73	67	63	81	72	67	63	71	66	62	70	65	62	69	65	61	60				60
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	56				56
9	75	65	59	55	74	65	59	55	64	59	55	63	58	55	62	58	55	53				53
10	72	62	56	52	71	61	56	52	61	55	52	60	55	52	59	55	52	50				50

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	194502
5°	190072
10°	175325
15°	152464
20°	125241
25°	97457
30°	71960
35°	50647
40°	31602
45°	17118
50°	9279
55°	7952
60°	7149
65°	6123
70°	5193
75°	5338
80°	4546
85°	4529

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 17118 cd/sqm



TEST NUMBER: P1260789
 CATALOG NUMBER: P3AS20R459050D010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	80.0	12.2
10°-20°	185.7	28.4
20°-30°	184.3	28.2
30°-40°	118.7	18.2
40°-50°	45.7	7.0
50°-60°	18.6	2.8
60°-70°	11.8	1.8
70°-80°	6.3	1.0
80°-90°	2.0	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	449.9	68.9
0°-40°	568.6	87.1
0°-60°	632.9	96.9
0°-90°	652.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	652.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	887	
5°	864	80
15°	672	186
25°	403	184
35°	189	119
45°	55	46
55°	21	19
65°	12	12
75°	6	6
85°	2	2
90°	0	



TEST NUMBER: P1260789
CATALOG NUMBER: P3AS20R459050D010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	887.0
2.5°	882.5
5°	863.5
7.5°	830.9
10°	787.4
12.5°	733.1
15°	671.6
17.5°	604.6
20°	536.7
22.5°	467.9
25°	402.8
27.5°	341.2
30°	284.2
32.5°	234.4
35°	189.2
37.5°	148.4
40°	110.4
42.5°	79.6
45°	55.2
47.5°	37.1
50°	27.2
52.5°	22.6
55°	20.8
57.5°	18.1
60°	16.3
62.5°	13.6
65°	11.8
67.5°	10.0
70°	8.1
72.5°	7.2
75°	6.3
77.5°	4.5
80°	3.6
82.5°	2.7
85°	1.8
87.5°	0.9
90°	0.0

(END OF REPORT)