

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1261333

Luminaire Tested: P3AS02R109727DE010 E3DL1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1261333
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-3)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R109727DE010 E3DL1LI
Description: 3in Adjustable LED luminaire with, R10 optic, 2700K CCT AND, 97CRI , E3DL1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 195.0 lumens
Efficiency: N/A
Efficacy: 51.3 lumens/watt
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.43
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1261333

CATALOG NUMBER: P3AS02R109727DE010 E3DL1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1261333

CATALOG NUMBER: P3AS02R109727DE010 E3DL1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	112	110	108		112	110	108	106		106	104	103		102	101	100		99	98	97
2	110	106	103	100		108	104	101	99		101	99	97		98	96	95		96	94	93
3	106	101	97	93		104	99	96	93		97	94	91		94	92	90		92	90	88
4	102	96	92	88		100	95	91	88		93	89	87		91	88	86		89	87	85
5	98	92	87	84		97	91	87	83		89	85	83		88	84	82		86	83	81
6	95	88	83	80		94	87	83	80		86	82	79		85	81	79		83	80	78
7	92	85	80	77		91	84	80	76		83	79	76		82	78	76		81	78	75
8	89	81	77	74		88	81	77	73		80	76	73		79	75	73		78	75	73
9	86	79	74	71		85	78	74	71		77	73	71		77	73	70		76	73	70
10	84	76	71	68		83	76	71	68		75	71	68		74	71	68		74	70	68

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	166588
5°	147875
10°	102692
15°	60727
20°	34583
25°	19767
30°	10938
35°	5836
40°	3235
45°	1737
50°	1092
55°	879
60°	746
65°	675
70°	577
75°	678
80°	505
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1737 cd/sqm

TEST NUMBER: P1261333

CATALOG NUMBER: P3AS02R109727DE010 E3DL1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	57.1	29.3
10°-20°	75.4	38.7
20°-30°	38.8	19.9
30°-40°	14.6	7.5
40°-50°	4.8	2.4
50°-60°	2.1	1.1
60°-70°	1.3	0.7
70°-80°	0.8	0.4
80°-90°	0.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	171.3	87.9
0°-40°	185.9	95.3
0°-60°	192.7	98.8
0°-90°	195.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	195.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	760	
5°	672	57
15°	268	75
25°	82	39
35°	22	15
45°	6	5
55°	2	2
65°	1	1
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1261333

CATALOG NUMBER: P3AS02R109727DE010 E3DL1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	759.7
1°	758.2
2°	748.2
3°	729.2
4°	704.3
5°	671.8
6°	634.9
7°	594.5
8°	549.7
9°	505.3
10°	461.2
12.5°	354.9
15°	267.5
17.5°	200.2
20°	148.2
22.5°	110.6
25°	81.7
27.5°	59.5
30°	43.2
32.5°	30.6
35°	21.8
37.5°	15.6
40°	11.3
42.5°	8.1
45°	5.6
47.5°	4.1
50°	3.2
52.5°	2.6
55°	2.3
57.5°	1.9
60°	1.7
62.5°	1.5
65°	1.3
67.5°	1.1
70°	0.9
72.5°	0.9
75°	0.8
77.5°	0.6
80°	0.4
82.5°	0.4
85°	0.2
87.5°	0.0
90°	0.0

(END OF REPORT)