

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1260797

Luminaire Tested: P3AS20R509050D010 E3CB1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1260797
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-32)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R509050D010 E3CB1MW
Description: 3in Adjustable LED luminaire with, R50 optic, 5000K CCT AND, 90CRI , E3CB1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2526.9 lumens
Efficiency: N/A
Efficacy: 87.7 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1260797

CATALOG NUMBER: P3AS20R509050D010 E3CB1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1260797

CATALOG NUMBER: P3AS20R509050D010 E3CB1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	112	109	107	112	109	107	106	105	104	102	102	101	99	98	97	97	95		
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	90		
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	85		
4	100	94	89	85	99	92	88	85	90	87	84	88	85	83	87	84	82	80		
5	96	89	84	80	94	88	83	79	86	82	79	84	81	78	83	80	77	76		
6	92	84	79	75	91	83	79	75	82	78	74	81	77	74	79	76	73	72		
7	88	80	75	71	87	79	74	71	78	74	71	77	73	70	76	73	70	69		
8	85	76	71	67	83	76	71	67	75	70	67	74	70	67	73	69	66	65		
9	81	73	68	64	80	72	67	64	71	67	64	71	66	63	70	66	63	62		
10	78	69	64	61	77	69	64	61	68	64	61	68	63	61	67	63	60	59		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	880083
5°	864339
10°	829911
15°	761026
20°	671055
25°	514360
30°	279663
35°	89971
40°	21154
45°	2853
50°	2524
55°	2829
60°	2412
65°	2854
70°	2372
75°	3135
80°	2273
85°	4529

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 85°
Luminance: 4529 cd/sqm

TEST NUMBER: P1260797

CATALOG NUMBER: P3AS20R509050D010 E3CB1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	368.5	14.6
10°-20°	931.8	36.9
20°-30°	933.2	36.9
30°-40°	262.4	10.4
40°-50°	15.8	0.6
50°-60°	6.0	0.2
60°-70°	4.8	0.2
70°-80°	3.2	0.1
80°-90°	1.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2233.6	88.4
0°-40°	2495.9	98.8
0°-60°	2517.8	99.6
0°-90°	2526.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2526.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4014	
5°	3927	368
15°	3352	932
25°	2126	933
35°	336	262
45°	9	16
55°	7	6
65°	6	5
75°	4	3
85°	2	1
90°	0	

TEST NUMBER: P1260797

CATALOG NUMBER: P3AS20R509050D010 E3CB1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	4013.5
2.5°	3993.2
5°	3926.7
7.5°	3836.2
10°	3727.2
12.5°	3562.8
15°	3352.3
17.5°	3110.3
20°	2875.7
22.5°	2583.9
25°	2125.9
27.5°	1582.9
30°	1104.5
32.5°	666.8
35°	336.1
37.5°	158.8
40°	73.9
42.5°	27.7
45°	9.2
47.5°	7.4
50°	7.4
52.5°	7.4
55°	7.4
57.5°	5.5
60°	5.5
62.5°	5.5
65°	5.5
67.5°	3.7
70°	3.7
72.5°	3.7
75°	3.7
77.5°	1.8
80°	1.8
82.5°	1.8
85°	1.8
87.5°	0.0
90°	0.0

(END OF REPORT)