

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1261386

Luminaire Tested: P3AS02R159727DE010 E3D1H

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1261386
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-7)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R159727DE010 E3D1H
Description: 3in Adjustable LED luminaire with, R15 optic, 2700K CCT AND, 97CRI , E3D1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 264.0 lumens
Efficiency: N/A
Efficacy: 73.3 lumens/watt
Spacing Criteria (0/90/45): 0.3 / 0.3 / 0.29
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1261386
CATALOG NUMBER: P3AS02R159727DE010 E3D1H

Luminous Intensity Polar Plot





TEST NUMBER: P1261386
 CATALOG NUMBER: P3AS02R159727DE010 E3D1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 |
| RCR | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | 100 | 100 |
| 1 | 116 | 114 | 112 | 111 | 113 | 112 | 110 | 109 | 108 | 107 | 105 | 104 | 103 | 102 | 101 | 100 | 99 | 98 | 98 | 98 |
| 2 | 112 | 109 | 107 | 105 | 110 | 108 | 105 | 103 | 105 | 103 | 101 | 102 | 100 | 99 | 99 | 98 | 97 | 96 | 96 | 96 |
| 3 | 110 | 106 | 102 | 100 | 108 | 104 | 102 | 99 | 102 | 100 | 98 | 100 | 98 | 96 | 98 | 96 | 95 | 94 | 94 | 94 |
| 4 | 107 | 102 | 99 | 96 | 106 | 101 | 98 | 96 | 99 | 97 | 95 | 98 | 96 | 94 | 96 | 94 | 93 | 92 | 92 | 92 |
| 5 | 105 | 100 | 96 | 94 | 103 | 99 | 96 | 93 | 97 | 94 | 92 | 96 | 93 | 92 | 94 | 93 | 91 | 90 | 90 | 90 |
| 6 | 102 | 97 | 94 | 91 | 101 | 96 | 93 | 91 | 95 | 92 | 90 | 94 | 92 | 90 | 93 | 91 | 89 | 88 | 88 | 88 |
| 7 | 100 | 95 | 91 | 89 | 99 | 94 | 91 | 89 | 93 | 90 | 88 | 92 | 90 | 88 | 91 | 89 | 88 | 87 | 87 | 87 |
| 8 | 98 | 93 | 89 | 87 | 97 | 92 | 89 | 87 | 91 | 89 | 87 | 91 | 88 | 86 | 90 | 88 | 86 | 85 | 85 | 85 |
| 9 | 96 | 91 | 88 | 85 | 96 | 91 | 87 | 85 | 90 | 87 | 85 | 89 | 87 | 85 | 89 | 86 | 85 | 84 | 84 | 84 |
| 10 | 95 | 89 | 86 | 84 | 94 | 89 | 86 | 84 | 88 | 85 | 83 | 88 | 85 | 83 | 87 | 85 | 83 | 82 | 82 | 82 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 502723 |
| 5° | 409948 |
| 10° | 200753 |
| 15° | 61453 |
| 20° | 26019 |
| 25° | 11783 |
| 30° | 4583 |
| 35° | 2115 |
| 40° | 658 |
| 45° | 248 |
| 50° | 102 |
| 55° | 38 |
| 60° | 44 |
| 65° | 52 |
| 70° | 0 |
| 75° | 0 |
| 80° | 0 |
| 85° | 0 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 248 cd/sqm



TEST NUMBER: P1261386
 CATALOG NUMBER: P3AS02R159727DE010 E3D1H

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 145.0 | 54.9 |
| 10°-20° | 89.0 | 33.7 |
| 20°-30° | 23.9 | 9.1 |
| 30°-40° | 5.3 | 2.0 |
| 40°-50° | 0.7 | 0.3 |
| 50°-60° | 0.1 | 0.1 |
| 60°-70° | 0.1 | 0.0 |
| 70°-80° | 0.0 | 0.0 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 257.8 | 97.7 |
| 0°-40° | 263.1 | 99.6 |
| 0°-60° | 263.9 | 100.0 |
| 0°-90° | 264.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 264.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 2293 | |
| 5° | 1862 | 145 |
| 15° | 271 | 89 |
| 25° | 49 | 24 |
| 35° | 8 | 5 |
| 45° | 1 | 1 |
| 55° | 0 | 0 |
| 65° | 0 | 0 |
| 75° | 0 | 0 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P1261386
CATALOG NUMBER: P3AS02R159727DE010 E3D1H

CANDELA DISTRIBUTION (FULL):

| 0° | |
|-------|--------|
| 0° | 2292.6 |
| 1° | 2278.3 |
| 2° | 2232.3 |
| 3° | 2149.6 |
| 4° | 2024.9 |
| 5° | 1862.4 |
| 6° | 1678.5 |
| 7° | 1473.6 |
| 8° | 1285.4 |
| 9° | 1085.9 |
| 10° | 901.6 |
| 11° | 719.3 |
| 12° | 553.4 |
| 13° | 425.6 |
| 14° | 337.0 |
| 15° | 270.7 |
| 17.5° | 167.8 |
| 20° | 111.5 |
| 22.5° | 75.1 |
| 25° | 48.7 |
| 27.5° | 28.8 |
| 30° | 18.1 |
| 32.5° | 12.2 |
| 35° | 7.9 |
| 37.5° | 4.4 |
| 40° | 2.3 |
| 42.5° | 1.3 |
| 45° | 0.8 |
| 47.5° | 0.5 |
| 50° | 0.3 |
| 52.5° | 0.2 |
| 55° | 0.1 |
| 57.5° | 0.1 |
| 60° | 0.1 |
| 62.5° | 0.1 |
| 65° | 0.1 |
| 67.5° | 0.0 |
| 70° | 0.0 |
| 72.5° | 0.0 |
| 75° | 0.0 |
| 77.5° | 0.0 |
| 80° | 0.0 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |



TEST NUMBER: P1261386
CATALOG NUMBER: P3AS02R159727DE010 E3D1H

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)