

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1260828

Luminaire Tested: P3AS20R559050D010 E3CD1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1260828
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-36)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R559050D010 E3CD1MMS
Description: 3in Adjustable LED luminaire with, R55 optic, 5000K CCT AND, 90CRI , E3CD1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2457.0 lumens
Efficiency: N/A
Efficacy: 85.3 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1260828

CATALOG NUMBER: P3AS20R559050D010 E3CD1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1260828

CATALOG NUMBER: P3AS20R559050D010 E3CD1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	112	109	107	105	105	104	102		101	100	99		98
2	109	104	101	98	107	103	99	96	100	97	94		97	94	92		94
3	104	98	94	90	102	97	93	89	94	91	88		92	89	86		90
4	99	92	87	84	98	91	87	83	89	85	82		87	84	81		86
5	95	87	82	78	93	86	81	78	85	80	77		83	79	76		82
6	91	83	77	73	89	82	77	73	80	76	72		79	75	72		78
7	87	78	73	69	85	78	72	69	76	72	68		75	71	68		74
8	83	74	69	65	82	74	69	65	73	68	65		72	67	64		71
9	79	71	65	61	78	70	65	61	69	64	61		68	64	61		68
10	76	67	62	58	75	67	62	58	66	61	58		65	61	58		65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	681459
5°	675125
10°	702258
15°	692512
20°	638596
25°	519586
30°	315593
35°	109245
40°	31173
45°	14885
50°	6311
55°	2829
60°	3245
65°	2854
70°	2372
75°	3135
80°	2273
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14885 cd/sqm

TEST NUMBER: P1260828

CATALOG NUMBER: P3AS20R559050D010 E3CD1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	296.5	12.1
10°-20°	847.8	34.5
20°-30°	945.2	38.5
30°-40°	309.2	12.6
40°-50°	40.8	1.7
50°-60°	8.6	0.4
60°-70°	5.0	0.2
70°-80°	3.2	0.1
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2089.5	85.0
0°-40°	2398.7	97.6
0°-60°	2448.1	99.6
0°-90°	2457.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2457.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3108	
5°	3067	297
15°	3050	848
25°	2148	945
35°	408	309
45°	48	41
55°	7	9
65°	6	5
75°	4	3
85°	0	1
90°	0	

TEST NUMBER: P1260828

CATALOG NUMBER: P3AS20R559050D010 E3CD1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	3107.7
2.5°	3085.6
5°	3067.1
7.5°	3111.4
10°	3153.9
12.5°	3131.7
15°	3050.5
17.5°	2921.2
20°	2736.6
22.5°	2481.7
25°	2147.5
27.5°	1722.8
30°	1246.4
32.5°	764.5
35°	408.1
37.5°	206.8
40°	108.9
42.5°	70.2
45°	48.0
47.5°	33.2
50°	18.5
52.5°	11.1
55°	7.4
57.5°	7.4
60°	7.4
62.5°	5.5
65°	5.5
67.5°	3.7
70°	3.7
72.5°	3.7
75°	3.7
77.5°	1.8
80°	1.8
82.5°	1.8
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)