

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1261406

Luminaire Tested: P3AS02R159727DE010 E3DLP1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1261406
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R159727DE010 E3DLP1MW
Description: 3in Adjustable LED luminaire with, R15 optic, 2700K CCT AND, 97CRI , E3DLP1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 126.0 lumens
Efficiency: N/A
Efficacy: 35.0 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.61
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1261406

CATALOG NUMBER: P3AS02R159727DE010 E3DLP1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1261406

CATALOG NUMBER: P3AS02R159727DE010 E3DLP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	108	106		111	108	106	104		104	102	101		100	99	98		97	96	95
2	108	103	99	95		105	101	97	94		98	95	92		95	92	90		92	90	88
3	102	96	91	87		100	94	90	86		92	88	85		89	86	83		87	84	82
4	97	90	84	80		95	88	83	79		86	82	78		84	81	78		82	79	77
5	93	84	78	74		91	83	78	74		81	77	73		80	76	73		78	75	72
6	88	79	73	69		87	79	73	69		77	72	69		76	71	68		74	71	68
7	84	75	69	65		83	74	69	65		73	68	64		72	67	64		71	67	64
8	80	71	65	61		79	71	65	61		69	64	61		68	64	61		68	63	60
9	77	68	62	58		76	67	62	58		66	61	58		65	61	57		64	60	57
10	74	64	59	55		73	64	59	55		63	58	55		62	58	55		62	57	54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	54338
5°	50209
10°	40102
15°	30284
20°	23055
25°	17566
30°	12584
35°	8218
40°	5038
45°	3039
50°	2013
55°	1567
60°	1360
65°	1193
70°	1026
75°	1017
80°	758
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3039 cd/sqm

TEST NUMBER: P1261406

CATALOG NUMBER: P3AS02R159727DE010 E3DLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	20.2	16.0
10°-20°	37.3	29.6
20°-30°	33.2	26.3
30°-40°	19.6	15.6
40°-50°	8.1	6.4
50°-60°	3.8	3.0
60°-70°	2.3	1.8
70°-80°	1.2	0.9
80°-90°	0.3	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	90.7	72.0
0°-40°	110.3	87.6
0°-60°	122.2	97.0
0°-90°	126.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	126.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	248	
5°	228	20
15°	133	37
25°	73	33
35°	31	20
45°	10	8
55°	4	4
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1261406

CATALOG NUMBER: P3AS02R159727DE010 E3DLP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	247.8
1°	247.2
2°	245.3
3°	241.6
4°	235.5
5°	228.1
6°	220.2
7°	210.7
8°	200.9
9°	190.9
10°	180.1
12.5°	155.3
15°	133.4
17.5°	114.6
20°	98.8
22.5°	84.9
25°	72.6
27.5°	60.8
30°	49.7
32.5°	39.7
35°	30.7
37.5°	23.5
40°	17.6
42.5°	13.1
45°	9.8
47.5°	7.6
50°	5.9
52.5°	4.9
55°	4.1
57.5°	3.5
60°	3.1
62.5°	2.7
65°	2.3
67.5°	2.0
70°	1.6
72.5°	1.4
75°	1.2
77.5°	0.8
80°	0.6
82.5°	0.4
85°	0.2
87.5°	0.2
90°	0.0

(END OF REPORT)