

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1261466

Luminaire Tested: P3AS02R259727DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1261466
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R259727DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R25 optic, 2700K CCT AND, 97CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 131.0 lumens
Efficiency: N/A
Efficacy: 36.4 lumens/watt
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.68
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1261466

CATALOG NUMBER: P3AS02R259727DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1261466

CATALOG NUMBER: P3AS02R259727DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	101		100	99	98		97
2	107	102	98	95	105	101	97	94	97	94	92		94	92	90		92
3	102	95	90	86	100	94	89	86	91	87	84		89	86	83		87
4	97	89	84	79	95	88	83	79	86	81	78		84	80	77		82
5	92	84	78	74	91	83	77	73	81	76	73		79	75	72		78
6	88	79	73	69	86	78	72	68	77	72	68		75	71	67		74
7	84	74	68	64	82	74	68	64	72	67	64		71	67	63		70
8	80	70	65	60	79	70	64	60	69	64	60		68	63	60		67
9	76	67	61	57	75	66	61	57	65	60	57		65	60	57		64
10	73	64	58	54	72	63	58	54	62	57	54		62	57	54		61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	47562
5°	45631
10°	39968
15°	32123
20°	24689
25°	18678
30°	13496
35°	8968
40°	5439
45°	3163
50°	2013
55°	1644
60°	1447
65°	1297
70°	1026
75°	1017
80°	758
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3163 cd/sqm

TEST NUMBER: P1261466

CATALOG NUMBER: P3AS02R259727DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	18.9	14.4
10°-20°	39.1	29.9
20°-30°	35.4	27.0
30°-40°	21.3	16.2
40°-50°	8.5	6.5
50°-60°	3.9	3.0
60°-70°	2.4	1.8
70°-80°	1.2	0.9
80°-90°	0.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	93.4	71.3
0°-40°	114.7	87.5
0°-60°	127.0	97.0
0°-90°	131.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	131.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	217	
5°	207	19
15°	142	39
25°	77	35
35°	34	21
45°	10	8
55°	4	4
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1261466

CATALOG NUMBER: P3AS02R259727DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	216.9
1°	216.9
2°	215.9
3°	213.6
4°	210.8
5°	207.3
6°	202.8
7°	197.7
8°	191.8
9°	185.8
10°	179.5
11°	172.2
12°	164.6
13°	157.1
14°	149.5
15°	141.5
17.5°	122.7
20°	105.8
22.5°	90.5
25°	77.2
27.5°	64.7
30°	53.3
32.5°	42.9
35°	33.5
37.5°	25.5
40°	19.0
42.5°	13.9
45°	10.2
47.5°	7.8
50°	5.9
52.5°	4.9
55°	4.3
57.5°	3.7
60°	3.3
62.5°	2.7
65°	2.5
67.5°	2.0
70°	1.6
72.5°	1.4
75°	1.2
77.5°	1.0
80°	0.6
82.5°	0.4
85°	0.4
87.5°	0.2



TEST NUMBER: P1261466

CATALOG NUMBER: P3AS02R259727DE010 E3DLP1WMH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)