

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1260898

Luminaire Tested: P3AS20R659050D010 E3DL1WMH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1260898  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-43)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS20R659050D010 E3DL1WMH  
Description: 3in Adjustable LED luminaire with, R65 optic, 5000K CCT AND, 90CRI , E3DL1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1852.0 lumens  
Efficiency: N/A  
Efficacy: 64.3 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.88  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 28.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1260898  
CATALOG NUMBER: P3AS20R659050D010 E3DL1WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P1260898  
 CATALOG NUMBER: P3AS20R659050D010 E3DL1WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93			93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85			85
3	101	95	89	85	99	93	88	84	90	86	83	88	85	82	86	83	80	79			79
4	96	88	82	78	94	87	81	77	85	80	76	83	79	75	81	77	74	73			73
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	68			68
6	86	77	70	66	84	76	70	66	74	69	65	73	68	65	72	67	64	63			63
7	82	72	66	61	80	71	65	61	70	64	61	69	64	60	67	63	60	58			58
8	77	67	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55			55
9	74	64	57	53	72	63	57	53	62	57	53	61	56	53	60	56	53	51			51
10	70	60	54	50	69	59	54	50	59	53	50	58	53	50	57	53	49	48			48

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	436763
5°	431520
10°	415134
15°	388879
20°	349774
25°	296993
30°	232289
35°	165541
40°	108317
45°	66984
50°	34012
55°	12004
60°	10525
65°	10533
70°	9489
75°	9404
80°	9345
85°	9309

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 66984 cd/sqm



TEST NUMBER: P1260898  
 CATALOG NUMBER: P3AS20R659050D010 E3DL1WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	184.1	9.9
10°-20°	476.8	25.7
20°-30°	557.2	30.1
30°-40°	389.4	21.0
40°-50°	171.4	9.3
50°-60°	38.2	2.1
60°-70°	19.4	1.0
70°-80°	11.7	0.6
80°-90°	4.0	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1218.0	65.8
0°-40°	1607.3	86.8
0°-60°	1816.9	98.1
0°-90°	1852.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1852.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1992	
5°	1960	184
15°	1713	477
25°	1228	557
35°	618	389
45°	216	171
55°	31	38
65°	20	19
75°	11	12
85°	4	4
90°	0	

TEST NUMBER: P1260898

CATALOG NUMBER: P3AS20R659050D010 E3DL1WMH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1991.8
2.5°	1984.4
5°	1960.4
7.5°	1919.8
10°	1864.4
12.5°	1796.1
15°	1713.0
17.5°	1611.5
20°	1498.9
22.5°	1371.5
25°	1227.5
27.5°	1076.2
30°	917.4
32.5°	764.2
35°	618.4
37.5°	491.0
40°	378.4
42.5°	286.1
45°	216.0
47.5°	158.8
50°	99.7
52.5°	51.7
55°	31.4
57.5°	27.7
60°	24.0
62.5°	22.2
65°	20.3
67.5°	16.6
70°	14.8
72.5°	12.9
75°	11.1
77.5°	9.2
80°	7.4
82.5°	5.5
85°	3.7
87.5°	1.8
90°	0.0

(END OF REPORT)