

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1261515

Luminaire Tested: P3AS02R359727DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1261515
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-18)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R359727DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R35 optic, 2700K CCT AND, 97CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 81.0 lumens
Efficiency: N/A
Efficacy: 22.5 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1261515

CATALOG NUMBER: P3AS02R359727DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1261515

CATALOG NUMBER: P3AS02R359727DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	98	96		96
2	106	100	96	92	104	98	94	91	95	92	89		92	89	87		89
3	100	92	87	82	98	91	86	81	88	84	80		86	82	79		83
4	94	85	79	74	92	84	78	74	82	77	73		80	75	72		78
5	89	79	73	68	87	78	72	67	76	71	67		75	70	66		73
6	84	74	67	62	82	73	67	62	71	66	62		70	65	61		68
7	79	69	62	57	78	68	62	57	67	61	57		65	60	57		64
8	75	64	58	53	74	64	58	53	63	57	53		62	56	53		61
9	71	60	54	50	70	60	54	50	59	53	49		58	53	49		57
10	67	57	51	46	66	56	50	46	56	50	46		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	18507
5°	18116
10°	16967
15°	15233
20°	13254
25°	11275
30°	9444
35°	7522
40°	5439
45°	3442
50°	1876
55°	1300
60°	1228
65°	1141
70°	1090
75°	932
80°	884
85°	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3442 cd/sqm

TEST NUMBER: P1261515

CATALOG NUMBER: P3AS02R359727DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	7.7	9.5
10°-20°	18.7	23.1
20°-30°	21.4	26.4
30°-40°	17.4	21.5
40°-50°	8.8	10.9
50°-60°	3.3	4.0
60°-70°	2.2	2.7
70°-80°	1.2	1.5
80°-90°	0.4	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	47.7	58.9
0°-40°	65.1	80.5
0°-60°	77.2	95.3
0°-90°	81.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	81.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	84	
5°	82	8
15°	67	19
25°	47	21
35°	28	17
45°	11	9
55°	3	3
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1261515

CATALOG NUMBER: P3AS02R359727DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	84.4
1°	84.3
2°	84.1
3°	83.7
4°	83.1
5°	82.3
6°	81.3
7°	80.3
8°	79.0
9°	77.7
10°	76.2
11°	74.6
12°	72.9
13°	71.0
14°	69.0
15°	67.1
17.5°	62.0
20°	56.8
22.5°	51.4
25°	46.6
27.5°	41.9
30°	37.3
32.5°	32.7
35°	28.1
37.5°	23.5
40°	19.0
42.5°	14.8
45°	11.1
47.5°	8.0
50°	5.5
52.5°	4.0
55°	3.4
57.5°	3.1
60°	2.8
62.5°	2.5
65°	2.2
67.5°	1.9
70°	1.7
72.5°	1.4
75°	1.1
77.5°	0.9
80°	0.7
82.5°	0.5
85°	0.3
87.5°	0.2



TEST NUMBER: P1261515

CATALOG NUMBER: P3AS02R359727DE010 E3DLD1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)