

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1261525

Luminaire Tested: P3AS02R359727DE010 E3DLP1WH

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1261525  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-19)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS02R359727DE010 E3DLP1WH  
Description: 3in Adjustable LED luminaire with, R35 optic, 2700K CCT AND, 97CRI , E3DLP1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 213.9 lumens  
Efficiency: N/A  
Efficacy: 59.4 lumens/watt  
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.58  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 3.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1261525

CATALOG NUMBER: P3AS02R359727DE010 E3DLP1WH

### Luminous Intensity Polar Plot



TEST NUMBER: P1261525

CATALOG NUMBER: P3AS02R359727DE010 E3DLP1WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 0   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 100 |
| 1   | 114 | 112 | 109 | 107 | 112 | 109 | 107 | 106 | 105 | 104 | 102 |  | 102 | 100 | 99  |  | 95  |
| 2   | 109 | 105 | 101 | 98  | 107 | 103 | 100 | 97  | 100 | 97  | 95  |  | 97  | 95  | 93  |  | 90  |
| 3   | 105 | 99  | 95  | 91  | 103 | 98  | 94  | 90  | 95  | 92  | 89  |  | 93  | 90  | 88  |  | 85  |
| 4   | 100 | 94  | 89  | 85  | 99  | 93  | 88  | 85  | 91  | 87  | 84  |  | 89  | 85  | 83  |  | 80  |
| 5   | 96  | 89  | 84  | 80  | 95  | 88  | 83  | 80  | 86  | 82  | 79  |  | 85  | 81  | 78  |  | 77  |
| 6   | 92  | 85  | 80  | 76  | 91  | 84  | 79  | 76  | 83  | 78  | 75  |  | 81  | 78  | 75  |  | 73  |
| 7   | 89  | 81  | 76  | 72  | 88  | 80  | 75  | 72  | 79  | 75  | 72  |  | 78  | 74  | 71  |  | 70  |
| 8   | 85  | 77  | 72  | 69  | 84  | 77  | 72  | 69  | 76  | 71  | 68  |  | 75  | 71  | 68  |  | 67  |
| 9   | 82  | 74  | 69  | 66  | 81  | 74  | 69  | 65  | 73  | 68  | 65  |  | 72  | 68  | 65  |  | 64  |
| 10  | 79  | 71  | 66  | 63  | 78  | 71  | 66  | 63  | 70  | 66  | 63  |  | 69  | 65  | 62  |  | 61  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 107930 |
| 5°  | 103720 |
| 10° | 90379  |
| 15° | 69217  |
| 20° | 46321  |
| 25° | 28018  |
| 30° | 16078  |
| 35° | 8994   |
| 40° | 4780   |
| 45° | 2450   |
| 50° | 1194   |
| 55° | 918    |
| 60° | 877    |
| 65° | 726    |
| 70° | 769    |
| 75° | 678    |
| 80° | 758    |
| 85° | 503    |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
Vertical Angle: 45°  
Luminance: 2450 cd/sqm

TEST NUMBER: P1261525

CATALOG NUMBER: P3AS02R359727DE010 E3DLP1WH

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 42.9   | 20.0      |
| 10°-20°   | 83.1   | 38.8      |
| 20°-30°   | 54.4   | 25.4      |
| 30°-40°   | 22.1   | 10.3      |
| 40°-50°   | 6.6    | 3.1       |
| 50°-60°   | 2.2    | 1.0       |
| 60°-70°   | 1.5    | 0.7       |
| 70°-80°   | 0.9    | 0.4       |
| 80°-90°   | 0.3    | 0.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 180.4  | 84.3      |
| 0°-40°    | 202.4  | 94.6      |
| 0°-60°    | 211.3  | 98.8      |
| 0°-90°    | 213.9  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 213.9  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 492 |      |
| 5°  | 471 | 43   |
| 15° | 305 | 83   |
| 25° | 116 | 54   |
| 35° | 34  | 22   |
| 45° | 8   | 7    |
| 55° | 2   | 2    |
| 65° | 1   | 1    |
| 75° | 1   | 1    |
| 85° | 0   | 0    |
| 90° | 0   |      |

TEST NUMBER: P1261525

CATALOG NUMBER: P3AS02R359727DE010 E3DLP1WH

**CANDELA DISTRIBUTION (FULL):**

| 0°    |       |
|-------|-------|
| 0°    | 492.2 |
| 1°    | 491.4 |
| 2°    | 489.2 |
| 3°    | 484.7 |
| 4°    | 479.4 |
| 5°    | 471.2 |
| 6°    | 461.1 |
| 7°    | 449.7 |
| 8°    | 436.8 |
| 9°    | 422.2 |
| 10°   | 405.9 |
| 11°   | 387.8 |
| 12°   | 368.9 |
| 13°   | 347.7 |
| 14°   | 327.5 |
| 15°   | 304.9 |
| 17.5° | 250.2 |
| 20°   | 198.5 |
| 22.5° | 152.7 |
| 25°   | 115.8 |
| 27.5° | 86.3  |
| 30°   | 63.5  |
| 32.5° | 46.6  |
| 35°   | 33.6  |
| 37.5° | 23.8  |
| 40°   | 16.7  |
| 42.5° | 11.6  |
| 45°   | 7.9   |
| 47.5° | 5.3   |
| 50°   | 3.5   |
| 52.5° | 2.6   |
| 55°   | 2.4   |
| 57.5° | 2.2   |
| 60°   | 2.0   |
| 62.5° | 1.8   |
| 65°   | 1.4   |
| 67.5° | 1.2   |
| 70°   | 1.2   |
| 72.5° | 1.0   |
| 75°   | 0.8   |
| 77.5° | 0.6   |
| 80°   | 0.6   |
| 82.5° | 0.4   |
| 85°   | 0.2   |
| 87.5° | 0.2   |



TEST NUMBER: P1261525

CATALOG NUMBER: P3AS02R359727DE010 E3DLP1WH

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)