

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1261526

Luminaire Tested: P3AS02R359727DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1261526
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-17)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R359727DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R35 optic, 2700K CCT AND, 97CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 132.0 lumens
Efficiency: N/A
Efficacy: 36.7 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.72
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1261526
CATALOG NUMBER: P3AS02R359727DE010 E3DLP1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P1261526
 CATALOG NUMBER: P3AS02R359727DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	95	95	95	93
2	107	102	98	94	105	100	97	93	97	94	91	94	92	89	91	89	88	88	88	88	86
3	102	95	90	86	100	94	89	85	91	87	84	89	85	82	86	84	81	81	81	81	80
4	97	89	83	79	95	88	82	78	86	81	77	84	80	77	82	78	76	76	76	76	74
5	92	83	77	73	90	82	77	73	81	76	72	79	75	71	77	74	71	71	71	71	69
6	87	78	72	68	86	77	72	68	76	71	67	75	70	67	73	69	66	66	66	66	65
7	83	74	68	63	82	73	67	63	72	67	63	71	66	63	69	65	62	62	62	62	61
8	79	70	64	60	78	69	63	59	68	63	59	67	62	59	66	62	59	59	59	59	57
9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	56	56	56	56	54
10	72	63	57	53	71	62	57	53	61	56	53	61	56	53	60	56	53	53	53	53	51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	42431
5°	41382
10°	37831
15°	32123
20°	25412
25°	19235
30°	14002
35°	9476
40°	5811
45°	3349
50°	2013
55°	1644
60°	1447
65°	1245
70°	1026
75°	1017
80°	1010
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3349 cd/sqm

TEST NUMBER: P1261526
 CATALOG NUMBER: P3AS02R359727DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	17.4	13.2
10°-20°	39.0	29.6
20°-30°	36.5	27.6
30°-40°	22.3	16.9
40°-50°	8.8	6.7
50°-60°	3.9	3.0
60°-70°	2.4	1.8
70°-80°	1.3	1.0
80°-90°	0.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	92.9	70.4
0°-40°	115.2	87.3
0°-60°	127.9	96.9
0°-90°	132.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	132.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	194	
5°	188	17
15°	142	39
25°	80	36
35°	35	22
45°	11	9
55°	4	4
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1261526
CATALOG NUMBER: P3AS02R359727DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	193.5
1°	193.7
2°	193.1
3°	191.9
4°	190.0
5°	188.0
6°	185.4
7°	182.3
8°	178.7
9°	174.6
10°	169.9
11°	165.0
12°	159.8
13°	154.1
14°	147.8
15°	141.5
17.5°	125.2
20°	108.9
22.5°	93.3
25°	79.5
27.5°	66.7
30°	55.3
32.5°	44.7
35°	35.4
37.5°	27.0
40°	20.3
42.5°	14.6
45°	10.8
47.5°	7.7
50°	5.9
52.5°	4.9
55°	4.3
57.5°	3.7
60°	3.3
62.5°	2.8
65°	2.4
67.5°	2.0
70°	1.6
72.5°	1.4
75°	1.2
77.5°	1.0
80°	0.8
82.5°	0.6
85°	0.4
87.5°	0.2



TEST NUMBER: P1261526
CATALOG NUMBER: P3AS02R359727DE010 E3DLP1WMH

CANDELA DISTRIBUTION (continued):

90° | $\frac{0^\circ}{0.0}$

(END OF REPORT)