

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1260943

Luminaire Tested: P3AS24R159050D010 E3D1LI

Issue Date: 1/29/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1260943  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-7)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS24R159050D010 E3D1LI  
Description: 3in Adjustable LED luminaire with, R15 optic, 5000K CCT AND, 90CRI , E3D1LI TRIM  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2669.0 lumens  
Efficiency: N/A  
Efficacy: 92.7 lumens/watt  
Spacing Criteria (0/90/45): 0.3 / 0.3 / 0.29  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 28.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1260943  
CATALOG NUMBER: P3AS24R159050D010 E3D1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P1260943  
 CATALOG NUMBER: P3AS24R159050D010 E3D1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	116	114	112	111	113	112	110	109	108	107	105	104	103	102	101	100	99	98	98	98	98
2	112	109	107	105	110	108	105	103	105	103	101	102	100	99	99	98	97	96	96	96	96
3	110	106	102	100	108	104	102	99	102	100	98	100	98	96	98	96	95	94	94	94	94
4	107	102	99	96	106	101	98	96	99	97	95	98	96	94	96	94	93	92	92	92	92
5	105	100	96	94	103	99	96	93	97	94	92	96	93	92	94	93	91	90	90	90	90
6	102	97	94	91	101	96	93	91	95	92	90	94	92	90	93	91	89	88	88	88	88
7	100	95	91	89	99	94	91	89	93	90	88	92	90	88	91	89	88	87	87	87	87
8	98	93	89	87	97	92	89	87	91	89	87	91	88	86	90	88	86	85	85	85	85
9	96	91	88	85	96	91	87	85	90	87	85	89	87	85	89	86	85	84	84	84	84
10	95	89	86	84	94	89	86	84	88	85	83	88	85	83	87	85	83	82	82	82	82

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	5082466
5°	4144409
10°	2029689
15°	621252
20°	263083
25°	119015
30°	46387
35°	21415
40°	6670
45°	2512
50°	1023
55°	382
60°	439
65°	519
70°	0
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 2512 cd/sqm



TEST NUMBER: P1260943  
 CATALOG NUMBER: P3AS24R159050D010 E3D1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1465.5	54.9
10°-20°	899.3	33.7
20°-30°	241.6	9.1
30°-40°	53.2	2.0
40°-50°	7.5	0.3
50°-60°	1.3	0.0
60°-70°	0.6	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2606.4	97.7
0°-40°	2659.6	99.6
0°-60°	2668.4	100.0
0°-90°	2669.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2669.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	23178	
5°	18828	###
15°	2737	899
25°	492	242
35°	80	53
45°	8	7
55°	1	1
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1260943  
CATALOG NUMBER: P3AS24R159050D010 E3D1LI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	23177.9
1°	23033.2
2°	22568.6
3°	21731.7
4°	20471.7
5°	18828.1
6°	16969.0
7°	14898.3
8°	12995.7
9°	10978.7
10°	9115.5
11°	7271.6
12°	5594.6
13°	4303.2
14°	3406.5
15°	2736.6
17.5°	1696.2
20°	1127.4
22.5°	759.0
25°	491.9
27.5°	291.5
30°	183.2
32.5°	123.5
35°	80.0
37.5°	44.5
40°	23.3
42.5°	13.2
45°	8.1
47.5°	5.1
50°	3.0
52.5°	2.0
55°	1.0
57.5°	1.0
60°	1.0
62.5°	1.0
65°	1.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0



TEST NUMBER: P1260943  
CATALOG NUMBER: P3AS24R159050D010 E3D1LI

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)