

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1260978

Luminaire Tested: P3AS24R209050D010 E3D1WMH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1260978
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-8)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS24R209050D010 E3D1WMH
Description: 3in Adjustable LED luminaire with, R20 optic, 5000K CCT AND, 90CRI , E3D1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2588.0 lumens
Efficiency: N/A
Efficacy: 89.9 lumens/watt
Spacing Criteria (0/90/45): 0.35 / 0.35 / 0.34
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1260978

CATALOG NUMBER: P3AS24R209050D010 E3D1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1260978

CATALOG NUMBER: P3AS24R209050D010 E3D1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	114	112	110	113	111	110	108	107	106	105		104	103	102		100
2	112	109	106	104	110	107	105	103	104	102	101		101	100	98		99
3	109	105	102	99	107	104	101	98	101	99	97		99	97	95		97
4	106	101	98	95	105	100	97	95	99	96	94		97	95	93		95
5	104	98	95	92	102	98	94	92	96	93	91		95	92	90		93
6	101	96	92	89	100	95	92	89	94	91	89		93	90	88		92
7	99	93	90	87	98	93	89	87	92	89	86		91	88	86		90
8	97	91	87	85	96	91	87	85	90	87	85		89	86	84		88
9	95	89	85	83	94	89	85	83	88	85	83		87	84	83		87
10	93	87	84	81	92	87	83	81	86	83	81		86	83	81		85

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3925782
5°	3305340
10°	2064491
15°	771832
20°	264926
25°	110426
30°	52008
35°	23289
40°	11021
45°	5644
50°	2081
55°	382
60°	439
65°	519
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5644 cd/sqm

TEST NUMBER: P1260978

CATALOG NUMBER: P3AS24R209050D010 E3D1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1248.7	48.3
10°-20°	1028.6	39.7
20°-30°	233.7	9.0
30°-40°	59.5	2.3
40°-50°	14.9	0.6
50°-60°	1.9	0.1
60°-70°	0.6	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2511.0	97.0
0°-40°	2570.5	99.3
0°-60°	2587.4	100.0
0°-90°	2588.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2588.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	17903	
5°	15016	###
15°	3400	1029
25°	456	234
35°	87	60
45°	18	15
55°	1	2
65°	1	1
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1260978

CATALOG NUMBER: P3AS24R209050D010 E3D1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	17903.0
1°	17751.2
2°	17304.0
3°	16662.5
4°	15875.2
5°	15016.2
6°	14058.9
7°	13002.5
8°	11770.1
9°	10548.7
10°	9271.8
11°	7912.8
12°	6555.9
13°	5406.4
14°	4307.5
15°	3399.9
16°	2683.5
17°	2116.8
18°	1701.0
19°	1383.2
20°	1135.3
21°	949.1
22°	792.3
23°	658.7
24°	549.4
25°	456.4
27.5°	298.5
30°	205.4
32.5°	126.5
35°	87.0
37.5°	55.7
40°	38.5
42.5°	26.3
45°	18.2
47.5°	12.1
50°	6.1
52.5°	3.0
55°	1.0
57.5°	1.0
60°	1.0
62.5°	1.0
65°	1.0
67.5°	0.0
70°	0.0
72.5°	0.0



TEST NUMBER: P1260978

CATALOG NUMBER: P3AS24R209050D010 E3D1WMH

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)