

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1260981

Luminaire Tested: P3AS24R209050D010 E3DL1LI

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1260981  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-7)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS24R209050D010 E3DL1LI  
Description: 3in Adjustable LED luminaire with, R20 optic, 5000K CCT AND, 90CRI , E3DL1LI TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2136.0 lumens  
Efficiency: N/A  
Efficacy: 74.2 lumens/watt  
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.46  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 28.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1260981  
CATALOG NUMBER: P3AS24R209050D010 E3DL1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P1260981

CATALOG NUMBER: P3AS24R209050D010 E3DL1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	97	97	97	95
2	110	106	102	100	108	104	101	98	101	98	96	98	96	94	95	94	92	92	92	92	91
3	106	100	96	93	104	99	95	92	97	93	91	94	92	89	92	90	88	92	90	88	87
4	102	96	91	88	100	95	90	87	92	89	86	91	88	85	89	86	84	89	86	84	83
5	98	91	87	83	97	90	86	83	89	85	82	87	84	81	86	83	81	86	83	81	79
6	95	87	83	79	93	87	82	79	85	81	78	84	81	78	83	80	77	83	80	77	76
7	91	84	79	76	90	83	79	76	82	78	75	81	78	75	80	77	75	80	77	75	73
8	88	81	76	73	87	80	76	73	79	75	72	78	75	72	78	74	72	78	74	72	71
9	85	78	73	70	85	77	73	70	77	73	70	76	72	69	75	72	69	75	72	69	68
10	83	75	71	68	82	75	70	67	74	70	67	73	70	67	73	69	67	73	69	67	66

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1643399
5°	1493899
10°	1104077
15°	682978
20°	390027
25°	222666
30°	124880
35°	67940
40°	37213
45°	20467
50°	11974
55°	8678
60°	8157
65°	7472
70°	6604
75°	7032
80°	5177
85°	5284

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 20467 cd/sqm



TEST NUMBER: P1260981  
 CATALOG NUMBER: P3AS24R209050D010 E3DL1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	587.7	27.5
10°-20°	839.0	39.3
20°-30°	437.9	20.5
30°-40°	169.3	7.9
40°-50°	55.0	2.6
50°-60°	21.6	1.0
60°-70°	14.3	0.7
70°-80°	8.4	0.4
80°-90°	2.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1864.6	87.3
0°-40°	2033.9	95.2
0°-60°	2110.5	98.8
0°-90°	2136.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2136.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	7494	
5°	6787	588
15°	3008	839
25°	920	438
35°	254	169
45°	66	55
55°	23	22
65°	14	14
75°	8	8
85°	2	3
90°	0	



TEST NUMBER: P1260981  
CATALOG NUMBER: P3AS24R209050D010 E3DL1LI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	7494.5
1°	7480.1
2°	7391.4
3°	7255.2
4°	7044.7
5°	6786.8
6°	6481.4
7°	6143.0
8°	5750.9
9°	5369.2
10°	4958.5
12.5°	3941.2
15°	3008.5
17.5°	2251.3
20°	1671.4
22.5°	1238.1
25°	920.3
27.5°	678.9
30°	493.2
32.5°	357.0
35°	253.8
37.5°	183.6
40°	130.0
42.5°	92.9
45°	66.0
47.5°	47.5
50°	35.1
52.5°	26.8
55°	22.7
57.5°	20.6
60°	18.6
62.5°	16.5
65°	14.4
67.5°	12.4
70°	10.3
72.5°	10.3
75°	8.3
77.5°	6.2
80°	4.1
82.5°	4.1
85°	2.1
87.5°	2.1
90°	0.0

(END OF REPORT)