

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1261593

Luminaire Tested: P3AS02R509727DE010 E3D1WH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1261593
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-13)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R509727DE010 E3D1WH
Description: 3in Adjustable LED luminaire with, R50 optic, 2700K CCT AND, 97CRI , E3D1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 283.0 lumens
Efficiency: N/A
Efficacy: 78.6 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.77
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1261593

CATALOG NUMBER: P3AS02R509727DE010 E3D1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1261593

CATALOG NUMBER: P3AS02R509727DE010 E3D1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	114	112	109	107	112	110	108	106	105	104	102		102	101	99		95
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		90
3	105	99	95	91	103	98	94	90	95	92	89		93	90	88		85
4	100	94	89	85	99	92	88	85	90	87	84		88	85	83		80
5	96	89	84	80	94	88	83	79	86	82	79		84	81	78		76
6	92	84	79	75	91	83	78	75	82	78	74		81	77	74		72
7	88	80	75	71	87	79	74	71	78	74	70		77	73	70		68
8	84	76	71	67	83	76	71	67	75	70	67		74	69	66		65
9	81	73	67	64	80	72	67	64	71	67	63		70	66	63		62
10	78	69	64	61	77	69	64	61	68	64	60		67	63	60		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	98896
5°	96258
10°	91871
15°	83156
20°	71943
25°	59011
30°	33904
35°	10520
40°	2834
45°	992
50°	239
55°	76
60°	44
65°	52
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 992 cd/sqm

TEST NUMBER: P1261593

CATALOG NUMBER: P3AS02R509727DE010 E3D1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.0	14.5
10°-20°	101.5	35.9
20°-30°	106.7	37.7
30°-40°	30.5	10.8
40°-50°	3.0	1.1
50°-60°	0.2	0.1
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	249.2	88.0
0°-40°	279.7	98.8
0°-60°	282.9	100.0
0°-90°	283.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	283.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	451	
5°	437	41
15°	366	102
25°	244	107
35°	39	31
45°	3	3
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1261593

CATALOG NUMBER: P3AS02R509727DE010 E3D1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	451.0
1°	450.3
2°	448.3
3°	445.4
4°	441.5
5°	437.3
6°	432.8
7°	428.0
8°	423.5
9°	418.4
10°	412.6
11°	405.9
12°	398.2
13°	388.6
14°	378.2
15°	366.3
16°	353.8
17°	341.6
18°	329.1
19°	318.1
20°	308.3
21°	298.9
22°	288.3
23°	276.0
24°	261.6
25°	243.9
26°	224.8
27°	203.4
28°	182.1
29°	159.2
30°	133.9
31°	110.2
32°	88.5
32.5°	79.0
33°	69.4
34°	53.2
35°	39.3
36°	28.9
37°	21.5
37.5°	18.6
38°	16.1
39°	12.5
40°	9.9
42.5°	5.6
45°	3.2



TEST NUMBER: P1261593
CATALOG NUMBER: P3AS02R509727DE010 E3D1WH

CANDELA DISTRIBUTION (continued):

	0°
47.5°	1.8
50°	0.7
52.5°	0.3
55°	0.2
57.5°	0.2
60°	0.1
62.5°	0.1
65°	0.1
67.5°	0.1
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)