

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1261034

Luminaire Tested: P3AS24R309050D010 E3D1MW

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1261034  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-16)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS24R309050D010 E3D1MW  
Description: 3in Adjustable LED luminaire with, R30 optic, 5000K CCT AND, 90CRI , E3D1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2627.0 lumens  
Efficiency: N/A  
Efficacy: 91.2 lumens/watt  
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.47  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 28.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1261034  
CATALOG NUMBER: P3AS24R309050D010 E3D1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P1261034  
 CATALOG NUMBER: P3AS24R309050D010 E3D1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98	100
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	98	96	95	97
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	95	94	92	94
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	94	92	93	91	89	91
4	105	100	96	93	103	99	95	92	97	94	91	95	92	90	93	91	89	93	91	89	88
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	87	91	88	87	85
6	99	93	89	86	98	92	88	86	91	88	85	90	87	85	89	86	84	89	86	84	83
7	96	90	86	83	95	89	86	83	88	85	82	87	84	82	86	84	82	86	84	82	81
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	84	82	80	79
9	91	85	81	78	90	84	81	78	84	80	78	83	80	78	82	79	77	82	79	77	77
10	89	83	79	76	88	82	78	76	82	78	76	81	78	76	80	77	75	80	77	75	75

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	2139258
5°	2098828
10°	1857993
15°	1177169
20°	446826
25°	132298
30°	52236
35°	16008
40°	7099
45°	2574
50°	2115
55°	1567
60°	1798
65°	2127
70°	1346
75°	1779
80°	2652
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 80°  
 Luminance: 2652 cd/sqm



TEST NUMBER: P1261034  
 CATALOG NUMBER: P3AS24R309050D010 E3D1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	876.5	33.4
10°-20°	1366.0	52.0
20°-30°	317.2	12.1
30°-40°	49.1	1.9
40°-50°	8.4	0.3
50°-60°	3.9	0.1
60°-70°	3.3	0.1
70°-80°	2.2	0.1
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2559.7	97.4
0°-40°	2608.9	99.3
0°-60°	2621.2	99.8
0°-90°	2627.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2627.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	9756	
5°	9535	877
15°	5185	1366
25°	547	317
35°	60	49
45°	8	8
55°	4	4
65°	4	3
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P1261034  
CATALOG NUMBER: P3AS24R309050D010 E3D1MW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	9755.8
1°	9749.6
2°	9722.8
3°	9677.4
4°	9619.6
5°	9535.0
6°	9429.8
7°	9273.0
8°	9058.4
9°	8742.7
10°	8344.4
11°	7830.7
12°	7250.8
13°	6607.1
14°	5899.3
15°	5185.4
17.5°	3392.3
20°	1914.8
22.5°	978.1
25°	546.8
27.5°	336.3
30°	206.3
32.5°	111.4
35°	59.8
37.5°	39.2
40°	24.8
42.5°	14.4
45°	8.3
47.5°	6.2
50°	6.2
52.5°	4.1
55°	4.1
57.5°	4.1
60°	4.1
62.5°	4.1
65°	4.1
67.5°	2.1
70°	2.1
72.5°	2.1
75°	2.1
77.5°	2.1
80°	2.1
82.5°	0.0
85°	0.0
87.5°	0.0



TEST NUMBER: P1261034  
CATALOG NUMBER: P3AS24R309050D010 E3D1MW

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)