

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1261648

Luminaire Tested: P3AS02R609727DE010 E3D1H

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1261648
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R609727DE010 E3D1H
Description: 3in Adjustable LED luminaire with, R60 optic, 2700K CCT AND, 97CRI , E3D1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 244.0 lumens
Efficiency: N/A
Efficacy: 67.8 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1261648
CATALOG NUMBER: P3AS02R609727DE010 E3D1H

Luminous Intensity Polar Plot





TEST NUMBER: P1261648
 CATALOG NUMBER: P3AS02R609727DE010 E3D1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94	94	94	94
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88	88	88	88
3	103	97	92	88	101	96	91	88	93	89	86	91	87	85	88	86	84	82	82	82	82
4	98	91	85	81	96	90	85	81	88	83	80	86	82	79	84	81	78	77	77	77	77
5	93	85	80	75	92	84	79	75	83	78	74	81	77	74	79	76	73	72	72	72	72
6	89	80	74	70	87	79	74	70	78	73	70	77	72	69	75	71	69	67	67	67	67
7	85	76	70	66	83	75	69	65	74	69	65	72	68	65	71	67	64	63	63	63	63
8	81	71	65	61	79	71	65	61	70	65	61	69	64	61	68	64	61	59	59	59	59
9	77	67	62	58	76	67	61	58	66	61	57	65	61	57	64	60	57	56	56	56	56
10	73	64	58	54	72	63	58	54	63	58	54	62	57	54	61	57	54	53	53	53	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	63942
5°	60356
10°	58783
15°	57435
20°	53415
25°	47737
30°	36461
35°	21067
40°	8158
45°	3411
50°	751
55°	115
60°	88
65°	52
70°	64
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3411 cd/sqm



TEST NUMBER: P1261648
 CATALOG NUMBER: P3AS02R609727DE010 E3D1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	25.9	10.6
10°-20°	70.5	28.9
20°-30°	88.3	36.2
30°-40°	49.3	20.2
40°-50°	9.4	3.8
50°-60°	0.5	0.2
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	184.6	75.7
0°-40°	234.0	95.9
0°-60°	243.9	99.9
0°-90°	244.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	244.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	292	
5°	274	26
15°	253	70
25°	197	88
35°	79	49
45°	11	9
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1261648
CATALOG NUMBER: P3AS02R609727DE010 E3D1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	291.6
1°	290.4
2°	286.6
3°	282.1
4°	277.9
5°	274.2
6°	271.4
7°	269.0
8°	267.2
9°	265.5
10°	264.0
11°	262.5
12°	260.8
13°	258.7
14°	256.2
15°	253.0
16°	249.1
17°	244.7
18°	239.7
19°	234.1
20°	228.9
21°	223.3
22°	217.5
23°	211.4
24°	204.7
25°	197.3
26°	188.6
27°	179.0
28°	168.1
29°	156.5
30°	144.0
31°	131.5
32°	118.5
32.5°	111.4
33°	105.0
34°	91.7
35°	78.7
36°	66.9
37°	54.4
37.5°	48.7
38°	43.1
39°	34.7
40°	28.5
42.5°	17.4
45°	11.0



TEST NUMBER: P1261648
CATALOG NUMBER: P3AS02R609727DE010 E3D1H

CANDELA DISTRIBUTION (continued):

	0°
47.5°	6.1
50°	2.2
52.5°	0.5
55°	0.3
57.5°	0.2
60°	0.2
62.5°	0.1
65°	0.1
67.5°	0.1
70°	0.1
72.5°	0.1
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)