

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1261068

Luminaire Tested: P3AS24R359050D010 E3DL1MW

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1261068  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-19)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS24R359050D010 E3DL1MW  
Description: 3in Adjustable LED luminaire with, R35 optic, 5000K CCT AND, 90CRI , E3DL1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2169.0 lumens  
Efficiency: N/A  
Efficacy: 75.3 lumens/watt  
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.58  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 28.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1261068

CATALOG NUMBER: P3AS24R359050D010 E3DL1MW

### Luminous Intensity Polar Plot



TEST NUMBER: P1261068

CATALOG NUMBER: P3AS24R359050D010 E3DL1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 114 | 112 | 109 | 107 | 112 | 109 | 107 | 106 | 105 | 104 | 102 |  | 102 | 100 | 99  |  | 98  |
| 2   | 109 | 105 | 101 | 98  | 107 | 103 | 100 | 97  | 100 | 97  | 95  |  | 97  | 95  | 93  |  | 94  |
| 3   | 105 | 99  | 95  | 91  | 103 | 98  | 94  | 90  | 95  | 92  | 89  |  | 93  | 90  | 88  |  | 91  |
| 4   | 100 | 94  | 89  | 85  | 99  | 93  | 88  | 85  | 91  | 87  | 84  |  | 89  | 85  | 83  |  | 87  |
| 5   | 96  | 89  | 84  | 80  | 95  | 88  | 83  | 80  | 86  | 82  | 79  |  | 85  | 81  | 78  |  | 83  |
| 6   | 92  | 85  | 80  | 76  | 91  | 84  | 79  | 76  | 83  | 78  | 75  |  | 81  | 77  | 75  |  | 80  |
| 7   | 89  | 81  | 76  | 72  | 88  | 80  | 75  | 72  | 79  | 75  | 71  |  | 78  | 74  | 71  |  | 77  |
| 8   | 85  | 77  | 72  | 69  | 84  | 77  | 72  | 68  | 76  | 71  | 68  |  | 75  | 71  | 68  |  | 74  |
| 9   | 82  | 74  | 69  | 66  | 81  | 74  | 69  | 65  | 73  | 68  | 65  |  | 72  | 68  | 65  |  | 71  |
| 10  | 79  | 71  | 66  | 63  | 78  | 71  | 66  | 63  | 70  | 66  | 63  |  | 69  | 65  | 62  |  | 69  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |         |
|-----|---------|
|     | 0°      |
| 0°  | 1093947 |
| 5°  | 1051351 |
| 10° | 916037  |
| 15° | 701639  |
| 20° | 469414  |
| 25° | 284049  |
| 30° | 162987  |
| 35° | 91122   |
| 40° | 48434   |
| 45° | 24964   |
| 50° | 11974   |
| 55° | 9481    |
| 60° | 9034    |
| 65° | 7472    |
| 70° | 7950    |
| 75° | 7032    |
| 80° | 7829    |
| 85° | 5284    |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 24964 cd/sqm

TEST NUMBER: P1261068

CATALOG NUMBER: P3AS24R359050D010 E3DL1MW

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 434.6  | 20.0      |
| 10°-20°   | 842.2  | 38.8      |
| 20°-30°   | 551.4  | 25.4      |
| 30°-40°   | 223.7  | 10.3      |
| 40°-50°   | 67.1   | 3.1       |
| 50°-60°   | 22.8   | 1.1       |
| 60°-70°   | 15.3   | 0.7       |
| 70°-80°   | 9.0    | 0.4       |
| 80°-90°   | 3.1    | 0.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 1828.1 | 84.3      |
| 0°-40°    | 2051.7 | 94.6      |
| 0°-60°    | 2141.7 | 98.7      |
| 0°-90°    | 2169.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 2169.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 4989 |      |
| 5°  | 4776 | 435  |
| 15° | 3091 | 842  |
| 25° | 1174 | 551  |
| 35° | 340  | 224  |
| 45° | 80   | 67   |
| 55° | 25   | 23   |
| 65° | 14   | 15   |
| 75° | 8    | 9    |
| 85° | 2    | 3    |
| 90° | 0    |      |

TEST NUMBER: P1261068

CATALOG NUMBER: P3AS24R359050D010 E3DL1MW

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 4988.8 |
| 1°    | 4980.6 |
| 2°    | 4957.9 |
| 3°    | 4912.5 |
| 4°    | 4858.8 |
| 5°    | 4776.3 |
| 6°    | 4673.1 |
| 7°    | 4557.6 |
| 8°    | 4427.6 |
| 9°    | 4279.1 |
| 10°   | 4114.0 |
| 11°   | 3930.4 |
| 12°   | 3738.5 |
| 13°   | 3523.9 |
| 14°   | 3319.7 |
| 15°   | 3090.7 |
| 17.5° | 2535.7 |
| 20°   | 2011.6 |
| 22.5° | 1547.4 |
| 25°   | 1174.0 |
| 27.5° | 874.8  |
| 30°   | 643.7  |
| 32.5° | 472.5  |
| 35°   | 340.4  |
| 37.5° | 241.4  |
| 40°   | 169.2  |
| 42.5° | 117.6  |
| 45°   | 80.5   |
| 47.5° | 53.6   |
| 50°   | 35.1   |
| 52.5° | 26.8   |
| 55°   | 24.8   |
| 57.5° | 22.7   |
| 60°   | 20.6   |
| 62.5° | 18.6   |
| 65°   | 14.4   |
| 67.5° | 12.4   |
| 70°   | 12.4   |
| 72.5° | 10.3   |
| 75°   | 8.3    |
| 77.5° | 6.2    |
| 80°   | 6.2    |
| 82.5° | 4.1    |
| 85°   | 2.1    |
| 87.5° | 2.1    |



TEST NUMBER: P1261068

CATALOG NUMBER: P3AS24R359050D010 E3DL1MW

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)