

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1261678

Luminaire Tested: P3AS02R659727DE010 E3D1LI

Issue Date: 1/29/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1261678  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-16)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS02R659727DE010 E3D1LI  
Description: 3in Adjustable LED luminaire with, R65 optic, 2700K CCT AND, 97CRI , E3D1LI TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 243.0 lumens  
Efficiency: N/A  
Efficacy: 67.5 lumens/watt  
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.88  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 3.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1261678

CATALOG NUMBER: P3AS02R659727DE010 E3D1LI

### Luminous Intensity Polar Plot



TEST NUMBER: P1261678

CATALOG NUMBER: P3AS02R659727DE010 E3D1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|
| RF  | 20  |     |     |     | 20  |     |     |     |     | 20  |     |     |     |     | 20  |     |     |     |    | 20 |
| RC  | 80  |     |     |     | 70  |     |     |     |     | 50  |     |     |     |     | 30  |     |     |     |    | 10 |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    |
| 1   | 114 | 111 | 109 | 106 | 111 | 109 | 107 | 105 | 105 | 103 | 102 | 101 | 100 | 99  | 98  | 97  | 96  | 94  |    |    |
| 2   | 108 | 104 | 100 | 96  | 106 | 102 | 98  | 95  | 99  | 96  | 93  | 96  | 93  | 91  | 93  | 91  | 89  | 88  |    |    |
| 3   | 103 | 97  | 92  | 88  | 101 | 95  | 91  | 88  | 93  | 89  | 86  | 90  | 87  | 85  | 88  | 86  | 83  | 82  |    |    |
| 4   | 98  | 91  | 85  | 81  | 96  | 90  | 85  | 81  | 87  | 83  | 80  | 85  | 82  | 79  | 84  | 81  | 78  | 77  |    |    |
| 5   | 93  | 85  | 79  | 75  | 92  | 84  | 79  | 75  | 82  | 78  | 74  | 81  | 77  | 74  | 79  | 76  | 73  | 72  |    |    |
| 6   | 89  | 80  | 74  | 70  | 87  | 79  | 74  | 70  | 78  | 73  | 69  | 76  | 72  | 69  | 75  | 71  | 68  | 67  |    |    |
| 7   | 84  | 75  | 70  | 65  | 83  | 75  | 69  | 65  | 73  | 69  | 65  | 72  | 68  | 65  | 71  | 67  | 64  | 63  |    |    |
| 8   | 80  | 71  | 65  | 61  | 79  | 71  | 65  | 61  | 69  | 64  | 61  | 68  | 64  | 61  | 67  | 63  | 60  | 59  |    |    |
| 9   | 77  | 67  | 61  | 58  | 76  | 67  | 61  | 57  | 66  | 61  | 57  | 65  | 60  | 57  | 64  | 60  | 57  | 56  |    |    |
| 10  | 73  | 64  | 58  | 54  | 72  | 63  | 58  | 54  | 62  | 57  | 54  | 62  | 57  | 54  | 61  | 57  | 54  | 52  |    |    |

**AVERAGE LUMINANCE (cd/sqm):**

|     |       |
|-----|-------|
|     | 0°    |
| 0°  | 65104 |
| 5°  | 60466 |
| 10° | 58471 |
| 15° | 56345 |
| 20° | 52085 |
| 25° | 47470 |
| 30° | 36664 |
| 35° | 21255 |
| 40° | 8444  |
| 45° | 3597  |
| 50° | 853   |
| 55° | 115   |
| 60° | 88    |
| 65° | 52    |
| 70° | 64    |
| 75° | 0     |
| 80° | 0     |
| 85° | 0     |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
Vertical Angle: 45°  
Luminance: 3597 cd/sqm

TEST NUMBER: P1261678

CATALOG NUMBER: P3AS02R659727DE010 E3D1LI

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 25.9   | 10.7      |
| 10°-20°   | 69.2   | 28.5      |
| 20°-30°   | 87.5   | 36.0      |
| 30°-40°   | 49.8   | 20.5      |
| 40°-50°   | 9.9    | 4.1       |
| 50°-60°   | 0.5    | 0.2       |
| 60°-70°   | 0.1    | 0.1       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 182.6  | 75.1      |
| 0°-40°    | 232.4  | 95.6      |
| 0°-60°    | 242.9  | 99.9      |
| 0°-90°    | 243.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 243.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 297 |      |
| 5°  | 275 | 26   |
| 15° | 248 | 69   |
| 25° | 196 | 88   |
| 35° | 79  | 50   |
| 45° | 12  | 10   |
| 55° | 0   | 1    |
| 65° | 0   | 0    |
| 75° | 0   | 0    |
| 85° | 0   | 0    |
| 90° | 0   |      |

TEST NUMBER: P1261678

CATALOG NUMBER: P3AS02R659727DE010 E3D1LI

**CANDELA DISTRIBUTION (FULL):**

| 0°    |       |
|-------|-------|
| 0°    | 296.9 |
| 1°    | 294.7 |
| 2°    | 289.9 |
| 3°    | 284.4 |
| 4°    | 278.9 |
| 5°    | 274.7 |
| 6°    | 271.6 |
| 7°    | 269.1 |
| 8°    | 266.9 |
| 9°    | 264.7 |
| 10°   | 262.6 |
| 11°   | 260.3 |
| 12°   | 257.9 |
| 13°   | 255.0 |
| 14°   | 251.9 |
| 15°   | 248.2 |
| 16°   | 243.8 |
| 17°   | 239.0 |
| 18°   | 233.8 |
| 19°   | 228.3 |
| 20°   | 223.2 |
| 21°   | 218.0 |
| 22°   | 213.3 |
| 23°   | 208.4 |
| 24°   | 202.8 |
| 25°   | 196.2 |
| 26°   | 188.3 |
| 27°   | 178.8 |
| 28°   | 168.1 |
| 29°   | 156.7 |
| 30°   | 144.8 |
| 31°   | 131.7 |
| 32°   | 118.8 |
| 32.5° | 112.1 |
| 33°   | 105.6 |
| 34°   | 92.4  |
| 35°   | 79.4  |
| 36°   | 67.4  |
| 37°   | 55.5  |
| 37.5° | 49.4  |
| 38°   | 44.5  |
| 39°   | 36.1  |
| 40°   | 29.5  |
| 42.5° | 18.2  |
| 45°   | 11.6  |



TEST NUMBER: P1261678

CATALOG NUMBER: P3AS02R659727DE010 E3D1LI

**CANDELA DISTRIBUTION (continued):**

|       | 0°  |
|-------|-----|
| 47.5° | 6.8 |
| 50°   | 2.5 |
| 52.5° | 0.5 |
| 55°   | 0.3 |
| 57.5° | 0.2 |
| 60°   | 0.2 |
| 62.5° | 0.2 |
| 65°   | 0.1 |
| 67.5° | 0.1 |
| 70°   | 0.1 |
| 72.5° | 0.0 |
| 75°   | 0.0 |
| 77.5° | 0.0 |
| 80°   | 0.0 |
| 82.5° | 0.0 |
| 85°   | 0.0 |
| 87.5° | 0.0 |
| 90°   | 0.0 |

(END OF REPORT)