

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1261074

Luminaire Tested: P3AS24R359050D010 E3DLD1MW

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1261074  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-18)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS24R359050D010 E3DLD1MW  
Description: 3in Adjustable LED luminaire with, R35 optic, 5000K CCT AND, 90CRI , E3DLD1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1670.0 lumens  
Efficiency: N/A  
Efficacy: 58.0 lumens/watt  
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.87  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 28.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1261074  
CATALOG NUMBER: P3AS24R359050D010 E3DLD1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P1261074  
 CATALOG NUMBER: P3AS24R359050D010 E3DLD1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91			
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69			
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64			
6	84	74	67	62	82	73	67	62	71	66	61	70	65	61	68	64	61	59			
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55			
8	75	64	58	53	74	64	57	53	63	57	53	62	56	53	61	56	52	51			
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48			
10	67	57	51	46	66	56	50	46	56	50	46	55	50	46	54	49	46	45			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	381483
5°	373387
10°	349693
15°	313895
20°	273047
25°	232683
30°	194916
35°	155235
40°	112239
45°	71046
50°	38719
55°	26838
60°	25349
65°	23556
70°	22504
75°	19232
80°	18184
85°	15599

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 71046 cd/sqm



TEST NUMBER: P1261074  
 CATALOG NUMBER: P3AS24R359050D010 E3DLD1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	157.9	9.5
10°-20°	384.8	23.0
20°-30°	440.9	26.4
30°-40°	359.8	21.5
40°-50°	181.4	10.9
50°-60°	67.4	4.0
60°-70°	45.2	2.7
70°-80°	25.0	1.5
80°-90°	7.6	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	983.6	58.9
0°-40°	1343.4	80.4
0°-60°	1592.2	95.3
0°-90°	1670.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1670.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1740	
5°	1696	158
15°	1383	385
25°	962	441
35°	580	360
45°	229	181
55°	70	67
65°	45	45
75°	23	25
85°	6	8
90°	0	

TEST NUMBER: P1261074

CATALOG NUMBER: P3AS24R359050D010 E3DLD1MW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1739.7
1°	1737.6
2°	1733.5
3°	1725.2
4°	1712.9
5°	1696.3
6°	1675.7
7°	1655.1
8°	1628.2
9°	1601.4
10°	1570.5
11°	1537.4
12°	1502.4
13°	1463.1
14°	1421.9
15°	1382.7
17.5°	1277.4
20°	1170.1
22.5°	1060.7
25°	961.7
27.5°	864.7
30°	769.8
32.5°	674.8
35°	579.9
37.5°	485.0
40°	392.1
42.5°	305.4
45°	229.1
47.5°	165.1
50°	113.5
52.5°	82.5
55°	70.2
57.5°	64.0
60°	57.8
62.5°	51.6
65°	45.4
67.5°	39.2
70°	35.1
72.5°	28.9
75°	22.7
77.5°	18.6
80°	14.4
82.5°	10.3
85°	6.2
87.5°	4.1



TEST NUMBER: P1261074  
CATALOG NUMBER: P3AS24R359050D010 E3DLD1MW

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)