

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1261779

Luminaire Tested: P3AS05R129727DE010 E3DL1WMH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1261779  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-3)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS05R129727DE010 E3DL1WMH  
Description: 3in Adjustable LED luminaire with, R12 optic, 2700K CCT AND, 97CRI , E3DL1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 421.0 lumens  
Efficiency: N/A  
Efficacy: 55.4 lumens/watt  
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.43  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 7.6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1261779  
CATALOG NUMBER: P3AS05R129727DE010 E3DL1WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P1261779  
 CATALOG NUMBER: P3AS05R129727DE010 E3DL1WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	97	98	97	95
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	96	94	93	91
3	106	101	97	93	104	99	96	93	97	94	91	94	92	90	92	90	88	92	90	88	87
4	102	96	92	88	100	95	91	88	93	89	87	91	88	86	89	87	85	89	87	85	83
5	98	92	87	84	97	91	87	83	89	86	83	88	84	82	86	83	81	86	83	81	80
6	95	88	83	80	94	87	83	80	86	82	79	85	81	79	83	80	78	83	80	78	77
7	92	85	80	77	91	84	80	76	83	79	76	82	78	76	81	78	75	81	78	75	74
8	89	81	77	74	88	81	77	73	80	76	73	79	76	73	78	75	73	78	75	73	72
9	86	79	74	71	85	78	74	71	77	73	71	77	73	70	76	73	70	76	73	70	69
10	84	76	71	68	83	76	71	68	75	71	68	74	71	68	74	70	68	74	70	68	67

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	359642
5°	319238
10°	221706
15°	131102
20°	74673
25°	42680
30°	23624
35°	12582
40°	6956
45°	3783
50°	2354
55°	1873
60°	1623
65°	1453
70°	1282
75°	1356
80°	1010
85°	1006

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 3783 cd/sqm



TEST NUMBER: P1261779  
 CATALOG NUMBER: P3AS05R129727DE010 E3DL1WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	123.3	29.3
10°-20°	162.8	38.7
20°-30°	83.8	19.9
30°-40°	31.5	7.5
40°-50°	10.3	2.4
50°-60°	4.5	1.1
60°-70°	2.8	0.7
70°-80°	1.6	0.4
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	369.9	87.9
0°-40°	401.4	95.3
0°-60°	416.1	98.8
0°-90°	421.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	421.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1640	
5°	1450	123
15°	578	163
25°	176	84
35°	47	31
45°	12	10
55°	5	4
65°	3	3
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P1261779  
CATALOG NUMBER: P3AS05R129727DE010 E3DL1WMH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1640.1
1°	1636.9
2°	1615.4
3°	1574.4
4°	1520.5
5°	1450.3
6°	1370.8
7°	1283.6
8°	1186.7
9°	1091.0
10°	995.7
12.5°	766.1
15°	577.5
17.5°	432.3
20°	320.0
22.5°	238.9
25°	176.4
27.5°	128.6
30°	93.3
32.5°	66.1
35°	47.0
37.5°	33.7
40°	24.3
42.5°	17.4
45°	12.2
47.5°	8.9
50°	6.9
52.5°	5.7
55°	4.9
57.5°	4.1
60°	3.7
62.5°	3.2
65°	2.8
67.5°	2.4
70°	2.0
72.5°	2.0
75°	1.6
77.5°	1.2
80°	0.8
82.5°	0.8
85°	0.4
87.5°	0.0
90°	0.0

(END OF REPORT)