

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1261180

Luminaire Tested: P3AS24R559050D010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1261180
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-35)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS24R559050D010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R55 optic, 5000K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1103.0 lumens
Efficiency: N/A
Efficacy: 38.3 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.81
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1261180

CATALOG NUMBER: P3AS24R559050D010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1261180

CATALOG NUMBER: P3AS24R559050D010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	108	106	104	104	103	101		101	99	98		97
2	108	103	99	95	106	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	94	90	86	92	88	85		89	86	84		87
4	97	90	84	80	95	89	83	79	86	82	78		84	81	78		82
5	92	84	78	74	91	83	78	74	81	77	73		80	76	72		78
6	88	79	73	69	86	78	73	68	77	72	68		75	71	68		74
7	84	74	68	64	82	74	68	64	72	67	64		71	67	63		70
8	80	70	64	60	78	70	64	60	69	63	60		67	63	60		67
9	76	66	61	57	75	66	60	56	65	60	56		64	59	56		63
10	73	63	57	53	72	62	57	53	62	57	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	302870
5°	299801
10°	289529
15°	267607
20°	230927
25°	182406
30°	129387
35°	83440
40°	50122
45°	28251
50°	15181
55°	5429
60°	4868
65°	4722
70°	4552
75°	4321
80°	3788
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 28251 cd/sqm

TEST NUMBER: P1261180

CATALOG NUMBER: P3AS24R559050D010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.1	11.6
10°-20°	326.0	29.6
20°-30°	341.6	31.0
30°-40°	199.3	18.1
40°-50°	74.6	6.8
50°-60°	17.5	1.6
60°-70°	9.0	0.8
70°-80°	5.3	0.5
80°-90°	1.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	795.7	72.1
0°-40°	995.0	90.2
0°-60°	1087.2	98.6
0°-90°	1103.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1103.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1381	
5°	1362	128
15°	1179	326
25°	754	342
35°	312	199
45°	91	75
55°	14	18
65°	9	9
75°	5	5
85°	1	1
90°	0	

TEST NUMBER: P1261180

CATALOG NUMBER: P3AS24R559050D010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1381.2
2.5°	1377.2
5°	1362.0
7.5°	1337.7
10°	1300.3
12.5°	1247.7
15°	1178.8
17.5°	1091.8
20°	989.6
22.5°	875.3
25°	753.9
27.5°	629.4
30°	511.0
32.5°	403.7
35°	311.7
37.5°	236.8
40°	175.1
42.5°	125.5
45°	91.1
47.5°	65.8
50°	44.5
52.5°	25.3
55°	14.2
57.5°	12.1
60°	11.1
62.5°	10.1
65°	9.1
67.5°	8.1
70°	7.1
72.5°	6.1
75°	5.1
77.5°	4.0
80°	3.0
82.5°	2.0
85°	1.0
87.5°	1.0
90°	0.0

(END OF REPORT)