

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1261819

Luminaire Tested: P3AS05R159727DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1261819
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R159727DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R15 optic, 2700K CCT AND, 97CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 258.0 lumens
Efficiency: N/A
Efficacy: 35.8 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.61
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1261819

CATALOG NUMBER: P3AS05R159727DE010 E3DLP1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P1261819

CATALOG NUMBER: P3AS05R159727DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	106	111	108	106	104	104	102	101		100	99	98		97
2	108	103	98	95	105	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87
4	97	90	84	80	95	88	83	79	86	82	78		84	81	78		82
5	93	84	78	74	91	83	78	74	81	77	73		80	76	72		78
6	88	79	73	69	87	79	73	69	77	72	69		76	71	68		74
7	84	75	69	65	83	74	69	65	73	68	64		72	67	64		71
8	80	71	65	61	79	71	65	61	69	64	61		68	64	61		68
9	77	68	62	58	76	67	62	58	66	61	58		65	61	57		64
10	74	64	59	55	73	64	59	55	63	58	55		62	58	55		62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	111263
5°	102817
10°	82096
15°	62021
20°	47231
25°	35978
30°	25776
35°	16811
40°	10305
45°	6233
50°	4128
55°	3211
60°	2763
65°	2387
70°	2180
75°	2118
80°	1642
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 6233 cd/sqm

TEST NUMBER: P1261819

CATALOG NUMBER: P3AS05R159727DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.4	16.0
10°-20°	76.4	29.6
20°-30°	68.0	26.3
30°-40°	40.2	15.6
40°-50°	16.5	6.4
50°-60°	7.8	3.0
60°-70°	4.7	1.8
70°-80°	2.5	1.0
80°-90°	0.6	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	185.7	72.0
0°-40°	225.9	87.6
0°-60°	250.2	97.0
0°-90°	258.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	258.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	507	
5°	467	41
15°	273	76
25°	149	68
35°	63	40
45°	20	16
55°	8	8
65°	5	5
75°	2	2
85°	0	1
90°	0	

TEST NUMBER: P1261819

CATALOG NUMBER: P3AS05R159727DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	507.4
1°	506.1
2°	502.3
3°	494.8
4°	482.2
5°	467.1
6°	450.8
7°	431.5
8°	411.4
9°	390.9
10°	368.7
12.5°	318.0
15°	273.2
17.5°	234.6
20°	202.4
22.5°	173.9
25°	148.7
27.5°	124.4
30°	101.8
32.5°	81.3
35°	62.8
37.5°	48.2
40°	36.0
42.5°	26.8
45°	20.1
47.5°	15.5
50°	12.1
52.5°	10.1
55°	8.4
57.5°	7.1
60°	6.3
62.5°	5.4
65°	4.6
67.5°	4.2
70°	3.4
72.5°	2.9
75°	2.5
77.5°	1.7
80°	1.3
82.5°	0.8
85°	0.4
87.5°	0.4
90°	0.0

(END OF REPORT)