

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1261822

Luminaire Tested: P3AS05R159727DE010 E3PHLP1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1261822
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-5)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R159727DE010 E3PHLP1MW
Description: 3in Adjustable LED luminaire with, R15 optic, 2700K CCT AND, 97CRI , E3PHLP1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 195.0 lumens
Efficiency: N/A
Efficacy: 27.1 lumens/watt
Spacing Criteria (0/90/45): 0.51 / 0.51 / 0.6
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1261822
CATALOG NUMBER: P3AS05R159727DE010 E3PHLP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1261822
 CATALOG NUMBER: P3AS05R159727DE010 E3PHLP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	95	93	92	90			90
2	105	99	94	90	102	97	92	89	94	90	87	91	87	85	88	85	83	81			81
3	99	91	85	80	96	89	84	80	87	82	78	84	80	77	82	79	76	74			74
4	93	84	78	73	91	83	77	72	81	76	71	79	74	71	77	73	70	68			68
5	88	78	72	67	86	77	71	67	76	70	66	74	69	65	72	68	65	63			63
6	83	73	67	62	82	73	66	62	71	65	61	70	65	61	68	64	60	59			59
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55			55
8	75	65	59	54	74	65	58	54	63	58	54	62	57	54	61	57	53	52			52
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50	49			49
10	69	59	52	48	68	58	52	48	57	52	48	56	51	48	56	51	48	46			46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	72977
5°	67004
10°	53395
15°	39909
20°	30313
25°	22937
30°	16990
35°	12126
40°	8301
45°	5799
50°	4947
55°	4855
60°	5043
65°	5344
70°	5450
75°	5592
80°	6061
85°	6038

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 82.5°
 Luminance: 7056 cd/sqm



TEST NUMBER: P1261822
 CATALOG NUMBER: P3AS05R159727DE010 E3PHLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	27.0	13.8
10°-20°	49.3	25.3
20°-30°	43.7	22.4
30°-40°	28.6	14.7
40°-50°	15.3	7.8
50°-60°	11.6	5.9
60°-70°	10.0	5.1
70°-80°	6.8	3.5
80°-90°	2.8	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	119.9	61.5
0°-40°	148.5	76.2
0°-60°	175.4	90.0
0°-90°	195.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	195.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	333	
5°	304	27
15°	176	49
25°	95	44
35°	45	29
45°	19	15
55°	13	12
65°	10	10
75°	7	7
85°	2	3
90°	0	



TEST NUMBER: P1261822
CATALOG NUMBER: P3AS05R159727DE010 E3PHLP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	332.8
2.5°	325.0
5°	304.4
7.5°	274.2
10°	239.8
12.5°	206.6
15°	175.8
17.5°	151.0
20°	129.9
22.5°	111.1
25°	94.8
27.5°	80.3
30°	67.1
32.5°	55.6
35°	45.3
37.5°	36.2
40°	29.0
42.5°	23.0
45°	18.7
47.5°	16.3
50°	14.5
52.5°	13.9
55°	12.7
57.5°	12.1
60°	11.5
62.5°	10.9
65°	10.3
67.5°	9.1
70°	8.5
72.5°	7.2
75°	6.6
77.5°	5.4
80°	4.8
82.5°	4.2
85°	2.4
87.5°	1.2
90°	0.0

(END OF REPORT)