

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1261842

Luminaire Tested: P3AS05R209727DE010 E3DLD1MW

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1261842  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-6)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS05R209727DE010 E3DLD1MW  
Description: 3in Adjustable LED luminaire with, R20 optic, 2700K CCT AND, 97CRI , E3DLD1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 330.0 lumens  
Efficiency: N/A  
Efficacy: 45.8 lumens/watt  
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.83  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 7.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1261842  
CATALOG NUMBER: P3AS05R209727DE010 E3DLD1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P1261842  
 CATALOG NUMBER: P3AS05R209727DE010 E3DLD1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91			91
2	106	100	96	92	104	99	94	91	95	92	89	92	89	87	90	87	85	83			83
3	100	93	87	82	98	91	86	82	88	84	80	86	82	79	84	81	78	76			76
4	94	86	79	75	92	85	79	74	82	77	73	80	76	72	78	75	72	70			70
5	89	80	73	68	87	79	73	68	77	71	67	75	70	67	73	69	66	65			65
6	84	74	68	63	82	73	67	63	72	66	62	70	65	62	69	65	61	60			60
7	80	69	63	58	78	69	62	58	67	62	58	66	61	57	65	60	57	55			55
8	75	65	59	54	74	64	58	54	63	58	54	62	57	53	61	57	53	52			52
9	72	61	55	50	70	61	55	50	60	54	50	59	54	50	58	53	50	48			48
10	68	58	51	47	67	57	51	47	56	51	47	56	51	47	55	50	47	45			45

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	81616
5°	79441
10°	73078
15°	64336
20°	55165
25°	46358
30°	37474
35°	28509
40°	20267
45°	13397
50°	8290
55°	5467
60°	4956
65°	4566
70°	4296
75°	3897
80°	3662
85°	3271

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 13397 cd/sqm



TEST NUMBER: P1261842  
 CATALOG NUMBER: P3AS05R209727DE010 E3DLD1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	33.4	10.1
10°-20°	78.9	23.9
20°-30°	87.6	26.5
30°-40°	66.8	20.2
40°-50°	34.2	10.4
50°-60°	14.1	4.3
60°-70°	8.8	2.7
70°-80°	4.9	1.5
80°-90°	1.4	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	199.8	60.6
0°-40°	266.6	80.8
0°-60°	314.9	95.4
0°-90°	330.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	330.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	372	
5°	361	33
15°	283	79
25°	192	88
35°	106	67
45°	43	34
55°	14	14
65°	9	9
75°	5	5
85°	1	1
90°	0	



TEST NUMBER: P1261842  
CATALOG NUMBER: P3AS05R209727DE010 E3DLD1MW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	372.2
1°	372.7
2°	371.0
3°	368.9
4°	365.5
5°	360.9
6°	355.5
7°	349.6
8°	343.3
9°	335.8
10°	328.2
12.5°	306.4
15°	283.4
17.5°	259.9
20°	236.4
22.5°	212.9
25°	191.6
27.5°	170.2
30°	148.0
32.5°	127.0
35°	106.5
37.5°	88.4
40°	70.8
42.5°	55.8
45°	43.2
47.5°	32.7
50°	24.3
52.5°	18.0
55°	14.3
57.5°	13.0
60°	11.3
62.5°	10.1
65°	8.8
67.5°	7.5
70°	6.7
72.5°	5.4
75°	4.6
77.5°	3.8
80°	2.9
82.5°	2.1
85°	1.3
87.5°	0.4
90°	0.0

(END OF REPORT)