

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1261845

Luminaire Tested: P3AS05R209727DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1261845
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-7)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R209727DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R20 optic, 2700K CCT AND, 97CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 434.0 lumens
Efficiency: N/A
Efficacy: 60.3 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.46
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1261845
CATALOG NUMBER: P3AS05R209727DE010 E3DLP1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1261845
 CATALOG NUMBER: P3AS05R209727DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95		
2	110	106	102	100	108	104	101	98	101	98	96	98	96	94	95	94	92	91		
3	106	100	96	93	104	99	95	92	97	93	91	94	92	89	92	90	88	87		
4	102	96	91	88	100	95	90	87	92	89	86	91	88	85	89	86	84	83		
5	98	91	87	83	97	90	86	83	89	85	82	87	84	81	86	83	81	79		
6	95	87	83	79	93	87	82	79	85	81	78	84	81	78	83	80	77	76		
7	91	84	79	76	90	83	79	76	82	78	75	81	78	75	80	77	75	73		
8	88	81	76	73	87	80	76	73	79	75	72	78	75	72	78	74	72	71		
9	85	78	73	70	85	77	73	70	77	73	70	76	72	69	75	72	69	68		
10	83	75	71	68	82	75	70	67	74	70	67	73	70	67	73	69	67	66		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	333921
5°	303543
10°	224333
15°	138775
20°	79247
25°	45245
30°	25371
35°	13813
40°	7557
45°	4155
50°	2422
55°	1759
60°	1667
65°	1505
70°	1346
75°	1440
80°	1010
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4155 cd/sqm



TEST NUMBER: P1261845
 CATALOG NUMBER: P3AS05R209727DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	119.4	27.5
10°-20°	170.5	39.3
20°-30°	89.0	20.5
30°-40°	34.4	7.9
40°-50°	11.2	2.6
50°-60°	4.4	1.0
60°-70°	2.9	0.7
70°-80°	1.7	0.4
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	378.9	87.3
0°-40°	413.3	95.2
0°-60°	428.8	98.8
0°-90°	434.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	434.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1523	
5°	1379	119
15°	611	170
25°	187	89
35°	52	34
45°	13	11
55°	5	4
65°	3	3
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P1261845
CATALOG NUMBER: P3AS05R209727DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1522.8
1°	1519.8
2°	1501.8
3°	1474.1
4°	1431.4
5°	1379.0
6°	1316.9
7°	1248.1
8°	1168.5
9°	1090.9
10°	1007.5
12.5°	800.8
15°	611.3
17.5°	457.4
20°	339.6
22.5°	251.6
25°	187.0
27.5°	137.9
30°	100.2
32.5°	72.5
35°	51.6
37.5°	37.3
40°	26.4
42.5°	18.9
45°	13.4
47.5°	9.6
50°	7.1
52.5°	5.5
55°	4.6
57.5°	4.2
60°	3.8
62.5°	3.4
65°	2.9
67.5°	2.5
70°	2.1
72.5°	2.1
75°	1.7
77.5°	1.3
80°	0.8
82.5°	0.8
85°	0.4
87.5°	0.4
90°	0.0

(END OF REPORT)