

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1261848

Luminaire Tested: P3AS05R209727DE010 E3PHLP1MW

Issue Date: 1/29/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1261848  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-6)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS05R209727DE010 E3PHLP1MW  
Description: 3in Adjustable LED luminaire with, R20 optic, 2700K CCT AND, 97CRI , E3PHLP1MW TRIM  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 205.0 lumens  
Efficiency: N/A  
Efficacy: 28.5 lumens/watt  
Spacing Criteria (0/90/45): 0.55 / 0.55 / 0.63  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 7.2  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1261848  
CATALOG NUMBER: P3AS05R209727DE010 E3PHLP1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P1261848  
 CATALOG NUMBER: P3AS05R209727DE010 E3PHLP1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	112	108	105	102	109	106	103	101	102	100	97	98	96	95	95	93	92	90	90	90	90
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81	81	81	81
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74	74	74	74
4	93	84	78	73	91	83	77	73	81	76	72	79	74	71	77	73	70	68	68	68	68
5	88	79	72	67	86	78	71	67	76	70	66	74	69	66	72	68	65	63	63	63	63
6	84	74	67	62	82	73	66	62	71	66	61	70	65	61	68	64	61	59	59	59	59
7	79	69	63	58	78	68	62	58	67	62	57	66	61	57	65	60	57	55	55	55	55
8	76	65	59	54	74	65	58	54	64	58	54	62	57	54	61	57	53	52	52	52	52
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50	49	49	49	49
10	69	59	52	48	68	58	52	48	57	52	48	57	52	48	56	51	48	46	46	46	46

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	72911
5°	67995
10°	56423
15°	43156
20°	32389
25°	24389
30°	18028
35°	12608
40°	8645
45°	5985
50°	5151
55°	5085
60°	5307
65°	5344
70°	5386
75°	5592
80°	6061
85°	6038

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 82.5°  
 Luminance: 7056 cd/sqm



TEST NUMBER: P1261848  
 CATALOG NUMBER: P3AS05R209727DE010 E3PHLP1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	27.7	13.5
10°-20°	52.8	25.8
20°-30°	46.5	22.7
30°-40°	30.0	14.6
40°-50°	15.9	7.8
50°-60°	12.0	5.8
60°-70°	10.2	5.0
70°-80°	7.1	3.5
80°-90°	2.8	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	127.0	62.0
0°-40°	157.0	76.6
0°-60°	184.9	90.2
0°-90°	205.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	205.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	332	
5°	309	28
15°	190	53
25°	101	47
35°	47	30
45°	19	16
55°	13	12
65°	10	10
75°	7	7
85°	2	3
90°	0	



TEST NUMBER: P1261848  
CATALOG NUMBER: P3AS05R209727DE010 E3PHLP1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	332.5
2.5°	325.8
5°	308.9
7.5°	283.0
10°	253.4
12.5°	220.8
15°	190.1
17.5°	162.3
20°	138.8
22.5°	118.9
25°	100.8
27.5°	85.1
30°	71.2
32.5°	58.5
35°	47.1
37.5°	38.0
40°	30.2
42.5°	24.1
45°	19.3
47.5°	16.9
50°	15.1
52.5°	13.9
55°	13.3
57.5°	12.7
60°	12.1
62.5°	10.9
65°	10.3
67.5°	9.7
70°	8.4
72.5°	7.8
75°	6.6
77.5°	6.0
80°	4.8
82.5°	4.2
85°	2.4
87.5°	1.2
90°	0.0

(END OF REPORT)