

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1261850

Luminaire Tested: P3AS05R259727DE010 E3CB1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1261850
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-12)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R259727DE010 E3CB1MMS
Description: 3in Adjustable LED luminaire with, R25 optic, 2700K CCT AND, 97CRI , E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 533.9 lumens
Efficiency: N/A
Efficacy: 74.2 lumens/watt
Spacing Criteria (0/90/45): 0.45 / 0.45 / 0.41
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1261850

CATALOG NUMBER: P3AS05R259727DE010 E3CB1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1261850

CATALOG NUMBER: P3AS05R259727DE010 E3CB1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	110	113	111	109	108	107	106	105		103	103	102		100
2	112	108	105	103	110	107	104	102	104	102	100		101	99	98		98
3	108	104	101	98	107	103	100	97	100	98	96		98	96	94		96
4	105	100	97	94	104	99	96	93	97	95	92		96	93	91		94
5	103	97	93	90	101	96	93	90	95	92	89		93	91	89		92
6	100	94	90	87	99	93	90	87	92	89	87		91	88	86		90
7	97	91	88	85	96	91	87	85	90	87	84		89	86	84		88
8	95	89	85	83	94	89	85	82	88	84	82		87	84	82		86
9	93	87	83	80	92	86	83	80	86	82	80		85	82	80		84
10	91	85	81	78	90	84	81	78	84	80	78		83	80	78		82

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	570919
5°	529517
10°	410658
15°	205904
20°	67649
25°	26905
30°	10103
35°	2918
40°	1317
45°	527
50°	443
55°	306
60°	351
65°	415
70°	256
75°	339
80°	505
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 527 cd/sqm

TEST NUMBER: P1261850

CATALOG NUMBER: P3AS05R259727DE010 E3CB1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	211.6	39.6
10°-20°	252.4	47.3
20°-30°	56.9	10.7
30°-40°	9.2	1.7
40°-50°	1.7	0.3
50°-60°	0.9	0.2
60°-70°	0.7	0.1
70°-80°	0.4	0.1
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	520.9	97.6
0°-40°	530.2	99.3
0°-60°	532.7	99.8
0°-90°	533.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	533.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2604	
5°	2406	212
15°	907	252
25°	111	57
35°	11	9
45°	2	2
55°	1	1
65°	1	1
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1261850

CATALOG NUMBER: P3AS05R259727DE010 E3CB1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	2603.6
1°	2599.4
2°	2578.4
3°	2539.9
4°	2481.5
5°	2405.6
6°	2315.0
7°	2216.8
8°	2104.4
9°	1981.5
10°	1844.3
11°	1686.1
12°	1504.0
13°	1313.6
14°	1109.2
15°	907.0
17.5°	516.9
20°	289.9
22.5°	174.9
25°	111.2
27.5°	68.4
30°	39.9
32.5°	21.0
35°	10.9
37.5°	7.1
40°	4.6
42.5°	2.9
45°	1.7
47.5°	1.3
50°	1.3
52.5°	1.3
55°	0.8
57.5°	0.8
60°	0.8
62.5°	0.8
65°	0.8
67.5°	0.8
70°	0.4
72.5°	0.4
75°	0.4
77.5°	0.4
80°	0.4
82.5°	0.0
85°	0.0
87.5°	0.0



TEST NUMBER: P1261850
CATALOG NUMBER: P3AS05R259727DE010 E3CB1MMS

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)