

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1261256

Luminaire Tested: P3AS24R709050D010 E3CB1MB

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1261256
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-48)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS24R709050D010 E3CB1MB
Description: 3in Adjustable LED luminaire with, R70 optic, 5000K CCT AND, 90CRI , E3CB1MB TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2582.0 lumens
Efficiency: N/A
Efficacy: 89.7 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.01 / 1.03
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1261256
CATALOG NUMBER: P3AS24R709050D010 E3CB1MB

Luminous Intensity Polar Plot





TEST NUMBER: P1261256
 CATALOG NUMBER: P3AS24R709050D010 E3CB1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93			93
2	107	102	97	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85			85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	85	82	80	78			78
4	95	87	81	77	94	86	81	76	84	79	75	82	78	75	80	77	74	72			72
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66			66
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61			61
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57			57
8	76	66	59	55	75	65	59	55	64	58	55	63	58	54	62	57	54	53			53
9	72	62	55	51	71	61	55	51	60	55	51	59	54	50	58	54	50	49			49
10	68	58	52	47	67	57	51	47	56	51	47	56	51	47	55	50	47	46			46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	512722
5°	489235
10°	465478
15°	453033
20°	436301
25°	412935
30°	384059
35°	322623
40°	207932
45°	96630
50°	25347
55°	6308
60°	6315
65°	5344
70°	5321
75°	5253
80°	5177
85°	5284

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 96630 cd/sqm



TEST NUMBER: P1261256
 CATALOG NUMBER: P3AS24R709050D010 E3CB1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	208.1	8.1
10°-20°	560.7	21.7
20°-30°	783.5	30.3
30°-40°	726.4	28.1
40°-50°	260.4	10.1
50°-60°	22.1	0.9
60°-70°	11.0	0.4
70°-80°	7.1	0.3
80°-90°	2.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1552.2	60.1
0°-40°	2278.6	88.3
0°-60°	2561.1	99.2
0°-90°	2582.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2582.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2338	
5°	2223	208
15°	1996	561
25°	1707	783
35°	1205	726
45°	312	260
55°	16	22
65°	10	11
75°	6	7
85°	2	3
90°	0	



TEST NUMBER: P1261256
CATALOG NUMBER: P3AS24R709050D010 E3CB1MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	2338.2
2.5°	2303.1
5°	2222.6
7.5°	2148.3
10°	2090.5
12.5°	2043.1
15°	1995.6
17.5°	1937.8
20°	1869.7
22.5°	1791.3
25°	1706.7
27.5°	1620.0
30°	1516.8
32.5°	1384.7
35°	1205.2
37.5°	976.1
40°	726.4
42.5°	495.3
45°	311.6
47.5°	173.4
50°	74.3
52.5°	24.8
55°	16.5
57.5°	14.4
60°	14.4
62.5°	12.4
65°	10.3
67.5°	10.3
70°	8.3
72.5°	8.3
75°	6.2
77.5°	6.2
80°	4.1
82.5°	4.1
85°	2.1
87.5°	2.1
90°	0.0

(END OF REPORT)