

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1261893

Luminaire Tested: P3AS05R309727DE010 E3DL1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1261893
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R309727DE010 E3DL1H
Description: 3in Adjustable LED luminaire with, R30 optic, 2700K CCT AND, 97CRI , E3DL1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 444.0 lumens
Efficiency: N/A
Efficacy: 61.7 lumens/watt
Spacing Criteria (0/90/45): 0.54 / 0.54 / 0.54
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1261893
CATALOG NUMBER: P3AS05R309727DE010 E3DL1H

Luminous Intensity Polar Plot





TEST NUMBER: P1261893
 CATALOG NUMBER: P3AS05R309727DE010 E3DL1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98	97
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	93	92
2	110	105	102	99	107	104	101	98	101	98	96	98	96	94	95	93	92	90	91	89	87
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	86	88	85	83
4	101	95	90	87	99	94	89	86	92	88	85	90	87	84	88	85	83	82	85	82	79
5	97	90	85	82	96	89	85	81	88	84	81	86	83	80	85	82	79	78	81	78	76
6	94	86	81	78	92	85	81	77	84	80	77	83	79	76	81	78	76	75	79	75	73
7	90	82	77	74	89	82	77	74	81	76	73	80	76	73	79	75	73	71	76	72	70
8	87	79	74	71	86	79	74	71	78	73	70	77	73	70	76	72	70	69	73	70	67
9	84	76	71	68	83	75	71	68	75	70	67	74	70	67	73	70	67	66	73	70	67
10	81	73	68	65	80	73	68	65	72	68	65	71	67	65	71	67	65	63	71	67	65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	259080
5°	246599
10°	207433
15°	149581
20°	92781
25°	52769
30°	29321
35°	15954
40°	8416
45°	4559
50°	2422
55°	1606
60°	1491
65°	1505
70°	1346
75°	1101
80°	1010
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4559 cd/sqm



TEST NUMBER: P1261893
 CATALOG NUMBER: P3AS05R309727DE010 E3DL1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.9	22.7
10°-20°	179.3	40.4
20°-30°	103.6	23.3
30°-40°	39.3	8.9
40°-50°	12.1	2.7
50°-60°	4.1	0.9
60°-70°	2.7	0.6
70°-80°	1.5	0.3
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	383.8	86.4
0°-40°	423.2	95.3
0°-60°	439.3	98.9
0°-90°	444.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	444.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1182	
5°	1120	101
15°	659	179
25°	218	104
35°	60	39
45°	15	12
55°	4	4
65°	3	3
75°	1	2
85°	0	0
90°	0	



TEST NUMBER: P1261893
CATALOG NUMBER: P3AS05R309727DE010 E3DL1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	1181.5
1°	1180.7
2°	1173.6
3°	1160.1
4°	1143.4
5°	1120.3
6°	1090.9
7°	1058.2
8°	1021.7
9°	978.1
10°	931.6
11°	881.2
12°	828.0
13°	772.2
14°	715.5
15°	658.9
17.5°	519.7
20°	397.6
22.5°	294.9
25°	218.1
27.5°	158.5
30°	115.8
32.5°	83.5
35°	59.6
37.5°	41.5
40°	29.4
42.5°	20.6
45°	14.7
47.5°	10.1
50°	7.1
52.5°	5.0
55°	4.2
57.5°	3.8
60°	3.4
62.5°	2.9
65°	2.9
67.5°	2.5
70°	2.1
72.5°	1.7
75°	1.3
77.5°	1.3
80°	0.8
82.5°	0.8
85°	0.4
87.5°	0.0



TEST NUMBER: P1261893
CATALOG NUMBER: P3AS05R309727DE010 E3DL1H

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)