

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246986

Luminaire Tested: P3AS13R459024DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1246986
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-25)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R459024DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R45 optic, 2400K CCT AND, 90CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 303.0 lumens
Efficiency: N/A
Efficacy: 20.8 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1246986

CATALOG NUMBER: P3AS13R459024DE010 E3DLP1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1246986

CATALOG NUMBER: P3AS13R459024DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97	96	94	93
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91	89	87	86
3	102	95	90	85	100	93	89	85	91	87	83		88	85	82		86	83	81	79
4	96	88	83	78	94	87	82	78	85	81	77		83	79	76		81	78	75	74
5	91	83	77	72	90	82	76	72	80	75	71		78	74	71		77	73	70	69
6	87	78	72	67	85	77	71	67	75	70	66		74	69	66		73	69	66	64
7	83	73	67	63	81	72	67	62	71	66	62		70	65	62		69	65	61	60
8	79	69	63	59	77	68	63	59	67	62	58		66	62	58		65	61	58	56
9	75	65	59	55	74	65	59	55	64	59	55		63	58	55		62	58	55	53
10	72	62	56	52	71	61	56	52	61	55	52		60	55	52		59	55	52	50

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	90256
5°	88201
10°	81361
15°	70738
20°	58105
25°	45220
30°	33398
35°	23503
40°	14656
45°	7939
50°	4298
55°	3708
60°	3333
65°	2854
70°	2436
75°	2457
80°	2147
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 7939 cd/sqm

TEST NUMBER: P1246986

CATALOG NUMBER: P3AS13R459024DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	37.1	12.2
10°-20°	86.1	28.4
20°-30°	85.5	28.2
30°-40°	55.1	18.2
40°-50°	21.2	7.0
50°-60°	8.6	2.9
60°-70°	5.5	1.8
70°-80°	2.9	1.0
80°-90°	0.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	208.8	68.9
0°-40°	263.9	87.1
0°-60°	293.7	96.9
0°-90°	303.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	303.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	412	
5°	401	37
15°	312	86
25°	187	86
35°	88	55
45°	26	21
55°	10	9
65°	6	5
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1246986

CATALOG NUMBER: P3AS13R459024DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	411.6
2.5°	409.5
5°	400.7
7.5°	385.5
10°	365.4
12.5°	340.2
15°	311.6
17.5°	280.5
20°	249.0
22.5°	217.1
25°	186.9
27.5°	158.3
30°	131.9
32.5°	108.8
35°	87.8
37.5°	68.9
40°	51.2
42.5°	37.0
45°	25.6
47.5°	17.2
50°	12.6
52.5°	10.5
55°	9.7
57.5°	8.4
60°	7.6
62.5°	6.3
65°	5.5
67.5°	4.6
70°	3.8
72.5°	3.4
75°	2.9
77.5°	2.1
80°	1.7
82.5°	1.3
85°	0.8
87.5°	0.4
90°	0.0

(END OF REPORT)