

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1261928

Luminaire Tested: P3AS05R359727DE010 E3DLD1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1261928
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-18)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R359727DE010 E3DLD1LI
Description: 3in Adjustable LED luminaire with, R35 optic, 2700K CCT AND, 97CRI , E3DLD1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 339.0 lumens
Efficiency: N/A
Efficacy: 47.1 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1261928

CATALOG NUMBER: P3AS05R359727DE010 E3DLD1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1261928

CATALOG NUMBER: P3AS05R359727DE010 E3DLD1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	98	96		96
2	106	100	96	92	104	98	94	91	95	92	89		92	89	87		89
3	100	92	87	82	98	91	86	81	88	84	80		86	82	79		83
4	94	85	79	74	92	84	78	74	82	77	73		80	75	72		78
5	89	79	73	68	87	78	72	67	76	71	67		75	70	66		73
6	84	74	67	62	82	73	67	62	71	66	61		70	65	61		68
7	79	69	62	57	78	68	62	57	67	61	57		65	60	57		64
8	75	64	58	53	74	64	57	53	63	57	53		62	56	53		61
9	71	60	54	50	70	60	54	50	59	53	49		58	53	49		57
10	67	57	51	46	66	56	50	46	56	50	46		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	77428
5°	75787
10°	70985
15°	63723
20°	55421
25°	47229
30°	39576
35°	31507
40°	22786
45°	14420
50°	7846
55°	5429
60°	5131
65°	4774
70°	4552
75°	3897
80°	3662
85°	3271

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14420 cd/sqm

TEST NUMBER: P1261928

CATALOG NUMBER: P3AS05R359727DE010 E3DLD1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	32.0	9.5
10°-20°	78.1	23.0
20°-30°	89.5	26.4
30°-40°	73.0	21.5
40°-50°	36.8	10.9
50°-60°	13.7	4.0
60°-70°	9.2	2.7
70°-80°	5.1	1.5
80°-90°	1.5	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	199.7	58.9
0°-40°	272.7	80.4
0°-60°	323.2	95.3
0°-90°	339.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	339.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	353	
5°	344	32
15°	281	78
25°	195	90
35°	118	73
45°	46	37
55°	14	14
65°	9	9
75°	5	5
85°	1	2
90°	0	

TEST NUMBER: P1261928

CATALOG NUMBER: P3AS05R359727DE010 E3DLD1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	353.1
1°	352.7
2°	351.9
3°	350.2
4°	347.7
5°	344.3
6°	340.2
7°	336.0
8°	330.5
9°	325.1
10°	318.8
11°	312.1
12°	305.0
13°	297.0
14°	288.6
15°	280.7
17.5°	259.3
20°	237.5
22.5°	215.3
25°	195.2
27.5°	175.5
30°	156.3
32.5°	137.0
35°	117.7
37.5°	98.4
40°	79.6
42.5°	62.0
45°	46.5
47.5°	33.5
50°	23.0
52.5°	16.8
55°	14.2
57.5°	13.0
60°	11.7
62.5°	10.5
65°	9.2
67.5°	8.0
70°	7.1
72.5°	5.9
75°	4.6
77.5°	3.8
80°	2.9
82.5°	2.1
85°	1.3
87.5°	0.8



TEST NUMBER: P1261928

CATALOG NUMBER: P3AS05R359727DE010 E3DLD1LI

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)