

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1247039

Luminaire Tested: P3AS13R559024DE010 E3DLD1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1247039
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-34)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R559024DE010 E3DLD1H
Description: 3in Adjustable LED luminaire with, R55 optic, 2400K CCT AND, 90CRI , E3DLD1H TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 726.0 lumens
Efficiency: N/A
Efficacy: 49.7 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.97
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1247039

CATALOG NUMBER: P3AS13R559024DE010 E3DLD1H

Luminous Intensity Polar Plot



TEST NUMBER: P1247039

CATALOG NUMBER: P3AS13R559024DE010 E3DLD1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					30					10					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	112	109	106	103		110	107	104	102		103	100	98		99	97	95		95	94	93
2	105	100	95	91		103	98	93	90		94	91	88		91	88	86		89	86	84
3	99	91	85	81		97	90	84	80		87	82	79		85	81	77		82	79	76
4	93	84	77	72		91	83	77	72		80	75	71		78	74	70		76	73	69
5	87	77	71	66		85	76	70	65		75	69	65		73	68	64		71	67	64
6	82	72	65	60		80	71	64	60		69	64	59		68	63	59		66	62	58
7	77	67	60	55		76	66	59	55		65	59	54		63	58	54		62	57	54
8	73	62	55	51		72	62	55	51		60	55	50		59	54	50		58	53	50
9	69	58	51	47		68	58	51	47		57	51	47		56	50	46		55	50	46
10	65	55	48	44		64	54	48	44		53	47	43		52	47	43		52	47	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	136502
5°	134756
10°	129457
15°	121068
20°	110446
25°	98546
30°	86190
35°	71608
40°	56449
45°	38299
50°	23402
55°	12119
60°	11271
65°	10689
70°	9873
75°	8727
80°	8713
85°	6542

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 38299 cd/sqm

TEST NUMBER: P1247039

CATALOG NUMBER: P3AS13R559024DE010 E3DLD1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	57.4	7.9
10°-20°	149.1	20.5
20°-30°	186.7	25.7
30°-40°	166.6	23.0
40°-50°	97.6	13.4
50°-60°	33.7	4.6
60°-70°	20.4	2.8
70°-80°	11.3	1.6
80°-90°	3.3	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	393.1	54.2
0°-40°	559.8	77.1
0°-60°	691.0	95.2
0°-90°	726.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	726.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	622	
5°	612	57
15°	533	149
25°	407	187
35°	268	167
45°	124	98
55°	32	34
65°	21	20
75°	10	11
85°	3	3
90°	0	

TEST NUMBER: P1247039

CATALOG NUMBER: P3AS13R559024DE010 E3DLD1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	622.5
2.5°	619.1
5°	612.2
7.5°	598.5
10°	581.4
12.5°	559.9
15°	533.3
17.5°	505.0
20°	473.3
22.5°	440.7
25°	407.3
27.5°	373.9
30°	340.4
32.5°	304.4
35°	267.5
37.5°	231.5
40°	197.2
42.5°	160.3
45°	123.5
47.5°	94.3
50°	68.6
52.5°	44.6
55°	31.7
57.5°	28.3
60°	25.7
62.5°	23.2
65°	20.6
67.5°	18.0
70°	15.4
72.5°	12.9
75°	10.3
77.5°	8.6
80°	6.9
82.5°	4.3
85°	2.6
87.5°	1.7
90°	0.0

(END OF REPORT)