

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1261969

Luminaire Tested: P3AS05R409727DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1261969
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-21)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R409727DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R40 optic, 2700K CCT AND, 97CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 308.0 lumens
Efficiency: N/A
Efficacy: 42.8 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.74
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1261969

CATALOG NUMBER: P3AS05R409727DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1261969

CATALOG NUMBER: P3AS05R409727DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	95	105	101	97	93	97	94	91		94	92	89		92
3	102	95	90	86	100	94	89	85	91	87	84		89	85	83		86
4	97	89	83	79	95	88	83	79	86	81	78		84	80	77		82
5	92	83	77	73	90	82	77	73	81	76	72		79	75	71		77
6	87	78	72	68	86	78	72	68	76	71	67		75	70	67		73
7	83	74	68	64	82	73	68	64	72	67	63		71	66	63		70
8	79	70	64	60	78	69	64	60	68	63	59		67	63	59		66
9	76	66	60	56	75	66	60	56	65	60	56		64	59	56		63
10	72	63	57	53	71	62	57	53	62	57	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	95913
5°	93968
10°	87484
15°	76255
20°	61442
25°	46067
30°	32385
35°	21228
40°	12853
45°	7660
50°	4571
55°	3670
60°	3289
65°	2854
70°	2693
75°	2118
80°	2147
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 7660 cd/sqm

TEST NUMBER: P1261969

CATALOG NUMBER: P3AS05R409727DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.6	12.9
10°-20°	92.5	30.0
20°-30°	87.2	28.3
30°-40°	50.4	16.4
40°-50°	20.1	6.5
50°-60°	8.9	2.9
60°-70°	5.5	1.8
70°-80°	2.9	0.9
80°-90°	0.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	219.3	71.2
0°-40°	269.8	87.6
0°-60°	298.7	97.0
0°-90°	308.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	308.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	437	
5°	427	40
15°	336	93
25°	190	87
35°	79	50
45°	25	20
55°	10	9
65°	6	6
75°	2	3
85°	1	1
90°	0	

TEST NUMBER: P1261969

CATALOG NUMBER: P3AS05R409727DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	437.4
2.5°	434.8
5°	426.9
7.5°	412.2
10°	392.9
12.5°	366.9
15°	335.9
17.5°	301.1
20°	263.3
22.5°	225.6
25°	190.4
27.5°	157.7
30°	127.9
32.5°	101.9
35°	79.3
37.5°	60.0
40°	44.9
42.5°	33.5
45°	24.7
47.5°	18.0
50°	13.4
52.5°	10.9
55°	9.6
57.5°	8.8
60°	7.5
62.5°	6.3
65°	5.5
67.5°	4.6
70°	4.2
72.5°	3.4
75°	2.5
77.5°	2.1
80°	1.7
82.5°	1.3
85°	0.8
87.5°	0.4
90°	0.0

(END OF REPORT)