

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1247127

Luminaire Tested: P3AS13R709024DE010 E3DLP1LI

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1247127  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-45)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R709024DE010 E3DLP1LI  
Description: 3in Adjustable LED luminaire with, R70 optic, 2400K CCT AND, 90CRI , E3DLP1LI TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 616.0 lumens  
Efficiency: N/A  
Efficacy: 42.2 lumens/watt  
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 14.6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1247127  
CATALOG NUMBER: P3AS13R709024DE010 E3DLP1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P1247127  
 CATALOG NUMBER: P3AS13R709024DE010 E3DLP1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92				92
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84				84
3	100	93	88	83	98	92	87	83	89	85	81	87	83	80	84	81	79	77				77
4	95	86	80	76	93	85	80	75	83	78	74	81	77	73	79	76	73	71				71
5	89	80	74	69	88	79	73	69	78	72	68	76	71	68	74	70	67	65				65
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	65	62	61				61
7	80	70	64	59	79	69	63	59	68	62	58	67	62	58	66	61	58	56				56
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52				52
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50	49				49
10	69	58	52	48	67	58	52	48	57	51	48	56	51	48	55	51	47	46				46

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	144484
5°	141844
10°	133754
15°	121385
20°	106176
25°	89570
30°	73328
35°	56885
40°	40705
45°	25770
50°	12861
55°	7875
60°	6754
65°	6226
70°	5514
75°	5083
80°	4293
85°	4277

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 25770 cd/sqm



TEST NUMBER: P1247127  
 CATALOG NUMBER: P3AS13R709024DE010 E3DLP1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	60.1	9.8
10°-20°	148.8	24.2
20°-30°	169.4	27.5
30°-40°	132.5	21.5
40°-50°	65.1	10.6
50°-60°	20.0	3.2
60°-70°	11.9	1.9
70°-80°	6.3	1.0
80°-90°	1.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	378.3	61.4
0°-40°	510.8	82.9
0°-60°	595.9	96.7
0°-90°	616.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	616.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	659	
5°	644	60
15°	535	149
25°	370	169
35°	212	132
45°	83	65
55°	21	20
65°	12	12
75°	6	6
85°	2	2
90°	0	

TEST NUMBER: P1247127  
CATALOG NUMBER: P3AS13R709024DE010 E3DLP1LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	658.9
2.5°	655.5
5°	644.4
7.5°	626.4
10°	600.7
12.5°	570.7
15°	534.7
17.5°	496.1
20°	455.0
22.5°	412.1
25°	370.2
27.5°	329.0
30°	289.6
32.5°	250.2
35°	212.5
37.5°	176.5
40°	142.2
42.5°	110.5
45°	83.1
47.5°	58.3
50°	37.7
52.5°	24.8
55°	20.6
57.5°	18.0
60°	15.4
62.5°	13.7
65°	12.0
67.5°	10.3
70°	8.6
72.5°	6.9
75°	6.0
77.5°	5.1
80°	3.4
82.5°	2.6
85°	1.7
87.5°	0.9
90°	0.0

(END OF REPORT)